

DTM04-2P-P006

✓ ACTIVE

DEUTSCH | DEUTSCH DT, DEUTSCH DTM


TE Internal #: DTM04-2P-P006

Housing for Male Terminals, Component-to-Wire, 2 Position, 4.19 mm [.165 in] Centerline, Sealable, Gray, Wire & Cable, Power, Hybrid

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings > DEUTSCH DTM Housings



Connector System: **Component-to-Wire**  
Number of Positions: **2**  
Connector & Housing Type: **Housing for Male Terminals**  
Centerline (Pitch): **4.19 mm [.165 in]**  
Sealable: **Yes**

[All DEUTSCH DTM Housings \(113\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector System	Component-to-Wire
Connector & Housing Type	Housing for Male Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Integrated in Housing

Configuration Features

Blank Cavity Position	0
Connector Modification	Terminating Resistor, J1939
Number of Positions	2
Number of Rows	1



Electrical Characteristics

Operating Voltage	250 VAC
Nominal Voltage Architecture	250 V

Body Features

Cable Exit Angle	180°
Primary Product Color	Gray
Connector & Keying Code	A

Contact Features

Contact Size	Size 20
Contact Type	Pin
Mating Pin Diameter	1.02 mm[.04 in]
Contact Current Rating (Max)	7.5 A

Mechanical Attachment

Terminal Position Assurance	Yes
Strain Relief	Add By Accessory
Mating Alignment Type	Keyed
Mating Alignment	With

Housing Features

Housing Material	PA GF
Centerline (Pitch)	4.19 mm[.165 in]

Dimensions

Connector Height	16.21 mm[.638 in]
Product Width	16.54 mm[.651 in]
Product Length	42.67 mm[1.68 in]
Compatible Insulation Diameter Range	1.35 – 3.05 mm[.053 – .12 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Degree of Protection	IP68, IP6K9K
----------------------	--------------



Compatible With Agency/Standards Products	SAE J2030
UL Flammability Rating	20mm Flame Test per Standard UL-94

Packaging Features

Packaging Quantity	1000
Packaging Method	Box

Other

Serviceable	No
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.5% in Component Part) Dodecamethylcyclohexasiloxane (D6) (.5% in Component Part) Decamethylcyclopentasiloxane (D5) (.5% in Component Part) Pb (1.2% in Component Part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability





Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on












requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # CAT-D485-CH8172 DEUTSCH DTM Housings</p>	 <p>TE Part # CAT-D487-M8649 DEUTSCH DT Mounting Clips</p>	 <p>TE Part # 1924487-2 MOUNTING CLIP, AMPSEAL 16</p>	 <p>TE Part # 1028-021-0205 BKSHL, 2P, BLK, REC, ST, NW 7.5/8.5</p>
---	--	--	--

Also in the Series | DEUTSCH DT

 <p>Automotive Connector Caps &amp; Covers (19)</p>	 <p>Automotive Connector Locks &amp; Position Assurance(87)</p>	 <p>Automotive Housings(706)</p>	 <p>Connector Backshells(61)</p>
 <p>Connector Seals &amp; Cavity Plugs(6)</p>	 <p>Connector Strain Relief(28)</p>	 <p>Insertion &amp; Extraction Tools(3)</p>	 <p>Other Automotive Connector Accessories(28)</p>
 <p>PCB Headers &amp; Receptacles(106)</p>			

Also in the Series | DEUTSCH DTM





Automotive Connector Caps & Covers (7)	Automotive Connector Locks & Position Assurance(25)	Automotive Housings(104)	Connector Backshells(7)
Connector Strain Relief(28)	Insertion & Extraction Tools(2)	PCB Headers & Receptacles(38)	

Customers Also Bought

TE Part #DTM06-2S PLG, 2P, GRY, N	TE Part #WM-2S WEDGE LOCK, 2P, PLG, ORG, DTM	TE Part #1563689-1 4POS,AMP MCP1.5K,REC HSG,ASSY	TE Part #1-936119-2 4POS MOS REC
TE Part #4-1393302-1 V23134A0052X278-EV-CBOX	TE Part #1-2236952-5 2POS, MCON 1.2 LL TAB SEALED COD A	TE Part #3-2236896-5 2POS, MCON 1.2 LL REC SEALED	TE Part #C885793001 FLHTC0311-20-9CK0073
TE Part #3315-016-0005 PROTECT CVR, 102/128P, PLG, YEL, DRB	TE Part #142316-1 MIC RECEPTACLE VRAC		

Documents



Product Drawings

REC, 2P, GRY, 120 OHM RESISTOR, AU, A

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_DTM04-2P-P006\_99.2d\_dxf.zip

English

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_DTM04-2P-P006\_99.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_DTM04-2P-P006\_99.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English