




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**
Wire Size: **2.1 – 3.31 mm²**
Mating Tab Width: **6.35 mm [.25 in]**
Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Compatible With Discrete Wire Type	Magnet Wire
------------------------------------	-------------

Configuration Features

Connection Capacity	Single
---------------------	--------

Contact Features

Quick Disconnect Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------



Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Terminal Material Thickness	.81 mm[.032 in]
Product Length	16 mm[.63 in]
Wire Size	2.1 – 3.31 mm²

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Packaging Features

Packaging Quantity	10000
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 60384-2 .250 FAST REC IS 1000 TPBR	 TE Part # 63497-1 AMPLIVAR TAB 032 TPBR	 TE Part # 63165-1 250 AMVAR FAST TAB 032TPBR	 TE Part # 60385-2 .250 FAST REC IS 18-2/17 TPBR
 TE Part # 1217029-1 CONTACT AMVAR 125 BLDE 020TPBR	 TE Part # 1217072-1 CONT AMVAR 125 BLADE 020 TPBR	 TE Part # 1217835-1 RECP AMVAR 250 FAST 016BR	 TE Part # 466510-1 HDM EAPR140F
 TE Part # 60384-1 .250 FAST REC IS 1000 BR	 TE Part # 63349-1 250 F TAB AMVAR 18-14 032TPBR	 TE Part # 63480-1 RCPT STATOR 27-22 0173PTPBR	 TE Part # 63497-2 AMPLIVAR TAB 032 TPBR
 TE Part # 63964-1 REC STATOR 2800/7400 PTPBR			

Also in the Series | AMPLIVAR

 Crimp Wire Pins, Tabs & Ferrules(5)	 Magnet Wire Terminals(4)	 PCB Terminals(1)	 Quick Disconnects(40)
---	------------------------------	----------------------	---------------------------



Ring Terminals(28)



Splices(76)

Customers Also Bought



TE Part #640455-3
03P MTA100 HDR ASSY SQ R/A POL




TE Part #3-794629-4
04P MICRO MNL ASSY,R/A,SMT,LF




TE Part #63486-1
MAG-MATE 110 FAST TAB 020 TPBR



TE Part #63854-2
250 PL MKIII REC. 18-14AWG TPBR



TE Part #62040-1
SPLC AMVAR 1500-5000 020TPBR




TE Part #2-2823088-5
25P,2MM,BRK HDR,SRVT,2.8,0.76AU, TB



TE Part #2176508-4
CJP 300W 1R0 5% Lead



TE Part #2176343-9
CRGCQ 1206 47R 1%



TE Part #2176344-6
CRGCQ 1206 6R8 5%



TE Part #CONN013-W
N Type Jack PCB Through Hole

Documents

Product Drawings

250 FAST TAB AMVAR 032TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_62922-1_M.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_62922-1_M.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_62922-1_M.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[FASTON Tabs](#)

English

Product Specifications

[Application Specification](#)

English

[Application Specification](#)

English