

HDP26-24-33SN-L017

✓ ACTIVE

DEUTSCH | [DEUTSCH HD](#), [DEUTSCH HDP](#)

TE Internal #: HDP26-24-33SN-L017

Housing for Female Terminals, Wire-to-Panel, 33 Position, Sealable, Black, Wire & Cable, Power, Panel Mount, -55 – 125 °C [-67 – 257 ° F], Hybrid

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings > DEUTSCH HDP20 Housings



Connector System: **Wire-to-Panel**
Number of Positions: **33**
Connector & Housing Type: **Housing for Female Terminals**
Sealable: **Yes**
Mating Pin Diameter: **1 mm [.04 in]**

[All DEUTSCH HDP20 Housings \(357\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Circular
Connector System	Wire-to-Panel
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Contact Retainer

Configuration Features

Blank Cavity Position	0
Connector Modification	Ring Adapter
Connector Seal Code	N Seal
Number of Positions	33

Electrical Characteristics

Operating Voltage	250 VAC
Nominal Voltage Architecture	250 V

Body Features



Cable Exit Angle	180°
Primary Product Color	Black

Contact Features

Contact Size	Size 20
Contact Type	Socket
Mating Pin Diameter	1 mm[.04 in]
Contact Current Rating (Max)	7.5 A

Mechanical Attachment

Terminal Position Assurance	No
Strain Relief	Without
Mating Alignment Type	Polarizing Slot
Mating Alignment	With
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	PA 66 GF
------------------	----------

Dimensions

Connector Height	42.5 mm[1.67 in]
Product Width	49.5 mm[1.95 in]
Product Length	49.5 mm[1.95 in]
Compatible Insulation Diameter Range	1.9 – 3.2 mm[.075 – .125 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Degree of Protection	IP67
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	40
Packaging Method	Tray



Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-D48-SP729
DEUTSCH Sealing Plugs



TE Part # CAT-H396-CH8172
DEUTSCH HDP20 Housings



TE Part # CAT-H396-B128
DEUTSCH HDP20 Backshells



TE Part # HD30-24BT-BK
BOOT, 24SZ, ST, BLK



TE Part # 0411-240-2005
EXT TOOL, SIZE 20, 16-22 AWG, N, RED

TE Part # HD30-24BT
BOOT, 24SZ, ST, GRY

TE Part # HD30-24BT-90-BK
BOOT, 24SZ, RA, BLK

Also in the Series | **DEUTSCH HD**

Automotive Connector Caps & Covers (32)

Automotive Housings(768)

Connector Backshells(29)

Connector Seals & Cavity Plugs(10)

Connector Strain Relief(5)

Insertion & Extraction Tools(11)

Other Automotive Connector Accessories(11)

PCB Headers & Receptacles(1)

Also in the Series | **DEUTSCH HDP**

Automotive Connector Caps & Covers (4)

Automotive Housings(357)

Connector Backshells(8)

Connector Seals & Cavity Plugs(1)



Insertion & Extraction Tools(11)



Other Automotive Connector Accessories(5)

Customers Also Bought



TE Part #HDP24-24-19SE-L017
DEUTSCH HDP20 Housings



TE Part #HDC26-24
DUST CAP, 24SZ, REC, BLK, HDP



TE Part #2428-011-2405
BKSHL, 24SZ, BLK, RA,NW17/19/26, L017,HDP



TE Part #0462-005-2031
SOC, SOLID, SIZE 20, 16-18AWG, AU



TE Part #9-2208656-9
58POS,MCON 1.2 CB,REC HSG,ASSY



TE Part #2500021-1
SRC Pwr 60+6AG Male Blade Hsg Assy

Documents

Product Drawings

PLG, 33P, BLK, N, RNG, 20, S

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_HDP26-24-33SN-L017_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_HDP26-24-33SN-L017_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_HDP26-24-33SN-L017_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English