

MATERIALS AND FINISHES


BODY, COUPLING NUT, CAP, OUTER CONTACT BRASS
PLATED NICKEL

CENTER CONTACT BRASS
PLATED GOLD

INSULATOR TEFLON

GASKET SILICONE RUBBER

N PLUG
INTERFACE



PART # 73276-0210

PS-73598-0032	ELECTRO/MECH PERFORM.
AS-89675-0800	CABLE INSTRUCTION
ES-73599-000-005	INTERFACE
SPECIFICATION	DESCRIPTION

CHG: NEW RELEASE

EC NO: URF2006-0538
DRWN:FLAHERTY 2006/05/31
CHKD:SSHAH 2006/05/31
APPR:JWIENER 2006/05/31

REV

QUALITY
SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0005
3 PLACES	± .005	± .0005
2 PLACES	± .005	± .0005
1 PLACE	± .005	± .0005

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY	DATE
TEF	1999/02/15
CHECKED BY	DATE
DHG	1999/02/15
APPROVED BY	DATE
GMH	1999/02/15

MATERIAL NO.
732760210

SIZE
C

SCALE
DESIGN UNITS
METRIC

THIRD ANGLE
PROJECTION

TITLE
N PLUG RA RG59 CRIMP
EWR-3116 50 OHM
N-PC/RA

MOLEX INCORPORATED

DOCUMENT NO.
SD-73276-021

SHEET NO.
1 OF 1