



Z-PACK 2mm HM

TE Internal #: 5646958-1
Header, Plug, Board-to-Board, 8 Position, 3 mm [.118 in] Centerline,
Printed Circuit Board, UL 94V-0, Z-PACK 2mm HM, Rectangular
Power Connectors

[View on TE.com >](#)

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Header**
Connector & Housing Type: **Plug**
Connector System: **Board-to-Board**
Number of Positions: **8**
Centerline (Pitch): **3 mm [.118 in]**

Features

Product Type Features

Header Type	Fully Shrouded
Rectangular Power Connector Type	Header
Connector & Housing Type	Plug
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	8
PCB Mount Orientation	Right Angle
Number of Power Positions	8
Number of Signal Positions	0
Number of Rows	0

Electrical Characteristics

Operating Voltage	30 VDC
-------------------	--------

Contact Features

PCB Contact Termination Area Plating Material Thickness	3.81 – 8.89 µm[150 – 350 µin]
Contact Mating Area Plating Material	Gold, Gold Flash over Palladium Nickel
Contact Underplating Material	Nickel



Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	10 A
Contact Retention Within Housing	With
Contact Type	Blade
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	.5 – 1.25 µm[19.68 – 49.21 µin]

Termination Features

Termination Post & Tail Length	3.43 mm[.135 in]
Termination Method to PCB	Through Hole - Press-Fit

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	3 mm[.118 in]
Housing Color	Gray
Housing Material	Polyester GF

Dimensions

PCB Thickness (Recommended)	1.6 mm[.063 in]
-----------------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Method	Box & Tube, Tube
------------------	------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | Z-PACK 2mm HM

Backplane Connector Housings(4)	Backplane Power Connectors(6)	Connector Caps & Covers(62)	Connector Contacts(2)
Connector Hardware(97)	Hard Metric Backplane Connectors (267)	High Speed Backplane Connectors(1)	Insertion & Extraction Tools(2)



Customers Also Bought

TE Part #1-178313-5
DYNAMIC D3100 HDR V 3P ASSY

TE Part #178289-7
DYNAMIC D3100 REC HSG 16P

TE Part #4-1625999-8
HSC100 6R8 5%

TE Part #2-1879075-8
Power Resistor: Aluminum Housed, 75 Watt

TE Part #1-1337481-0
SMB R/A PCB Skt 50Ohm Gold Plt

TE Part #6469085-1
HMZD 3PAIR, HDR ASSY, 25MM MOD

TE Part #2337815-1
MINISAS HD TO MINISAS HD,30AWG, 0.5M

TE Part #3-2176325-7
CRGP 0402 10K 1%

TE Part #4-2176326-9
CRGP 0603 100K 1%

Documents

Product Drawings
UPM EXPANDED PIN ASSEMBLY
English

CAD Files
3D PDF
English
Customer View Model
ENG_CVM_5646958-1_O.2d_dxf.zip



English

Customer View Model

[ENG_CVM_5646958-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_5646958-1_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[POWER_CONNECTORS_CATALOG_SEC01_BOARD_TO_BOARD](#)

English

[2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1](#)

English

Product Specifications

[Engineering Report](#)

English