



Connectors > Automotive Connectors > Automotive Housings > AMPSEAL 16 Housings



Connector System: **Wire-to-Wire**

Number of Positions: **2**

Connector & Housing Type: **Plug**

Centerline (Pitch): **4.5 mm [.177 in]**

Sealable: **Yes**

[All AMPSEAL 16 Housings \(224\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector System	Wire-to-Wire
Connector & Housing Type	Plug
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	2
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

Body Features

Cable Exit Angle	180°
Primary Product Color	Black
Connector & Keying Code	B



Contact Features

Contact Size	1.5mm
Contact Type	Socket
Mating Pin Diameter	1.5 mm[.06 in]

Mechanical Attachment

Terminal Position Assurance	Yes
Strain Relief	Add By Accessory
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PBT GF
Centerline (Pitch)	4.5 mm[.177 in]

Dimensions

Connector Height	23.5 mm[.925 in]
Product Width	36.75 mm[1.447 in]
Product Length	20.33 mm[.8 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Industry Standards

Degree of Protection	IP67
UL Flammability Rating	UL 94HB

Packaging Features

Packaging Quantity	27
Packaging Method	Tube

Other

Serviceable	Yes
Connector Position Assurance Capable	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # CAT-AM7801-B128
AMPSEAL 16 Connectors Backshell




TE Part # CAT-AM7801-CH8172
AMPSEAL 16 Housings




TE Part # CAT-AM7801-T273
AMPSEAL 16 CONTACTS




TE Part # CAT-AM7801-T618
Removal Tools — AMPSEAL 16



TE Part # 776364-1
SEALING PLUG, SZ 20 CAVITY



TE Part # 2203728-1
AS16; 2p Wire Seal; Reduced Diameter



TE Part # 2272179-1
AMPSEAL 16 PERIPHERAL SEAL 2P - SERVICE

Also in the Series | AMPSEAL 16



Automotive Connector Caps & Covers
(3)

Automotive Connector Locks &
Position Assurance(2)

Automotive Housings(244)

Automotive Terminals(35)

Connector Backshells(84)

Connector Seals & Cavity Plugs(4)

Data Connectivity Headers(2)

Data Connectivity Housings(3)

Other Automotive Connector
Accessories(11)

Customers Also Bought

TE Part #805M1-0020-01
805M1-0020-01 TO-5 Accelerometer

TE Part #776534-2
AMPSEAL 16 Housings

TE Part #1394522-2
MIXED SOCKET HOUSING, 42POS. ,

TE Part #6-1105151-1
HSS-C-Bu.Ag.25,0 qmm

Documents

Product Drawings
AS16,PLUG ASSY,ST,02P,E SEAL,CODE B

English

CAD Files
3D PDF
3D
Customer View Model



[ENG_CVM_CVM_776522-2_E_c-776522-2-e.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_776522-2_E_c-776522-2-e.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_776522-2_E_c-776522-2-e.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ICT Terminals and Connectors Catalogue](#)

English

[CONNECTOR SELECTOR](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English