



DEUTSCH | DEUTSCH DT

TE Internal #: DT04-08PA-CL07

Housing for Female Terminals, Wire-to-Wire, 8 Position, 9.09 mm [.358 in] Centerline, Sealable, Gray, Wire & Cable, Power, Panel Mount, DEUTSCH DT

[View on TE.com >](#)

Connectors > Automotive Connectors > Automotive Housings > DEUTSCH DT Receptacle Connectors



Connector System: **Wire-to-Wire**
Number of Positions: **8**
Connector & Housing Type: **Housing for Female Terminals**
Centerline (Pitch): **9.09 mm [.358 in]**
Sealable: **Yes**

[All DEUTSCH DT Receptacle Connectors \(247\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector System	Wire-to-Wire
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Integrated in Housing

Configuration Features

Blank Cavity Position	0
Connector Modification	Shrink Boot Adapter
Connector Seal Code	E Seal
Number of Positions	8
Number of Rows	2

Electrical Characteristics

Operating Voltage	250 VAC
Nominal Voltage Architecture	250 V

Body Features



Cable Exit Angle	180°
Primary Product Color	Gray
Connector & Keying Code	A

Contact Features

Contact Size	Size 16
Contact Type	Receptacle
Mating Pin Diameter	1.57 mm[.062 in]
Contact Current Rating (Max)	13 A

Mechanical Attachment

Terminal Position Assurance	Yes
Strain Relief	Add By Accessory
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	PA GF
Centerline (Pitch)	9.09 mm[.358 in]

Dimensions

Connector Height	38.1 mm[1.5 in]
Product Width	76.2 mm[3 in]
Product Length	60.91 mm[2.398 in]
Row-to-Row Spacing	4.45 mm[.175 in]
Compatible Insulation Diameter Range	1.35 – 3.05 mm[.053 – .12 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Degree of Protection	IP68, IP6K9K
Compatible With Agency/Standards Products	SAE J2030
UL Flammability Rating	12mm Flame Test per Standard UL-94



Packaging Features

Packaging Quantity	96
Packaging Method	Box

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.5% in Component Part) Dodecamethylcyclohexasiloxane (D6) (.5% in Component Part) Decamethylcyclopentasiloxane (D5) (.5% in Component Part) Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # CAT-J41-DDPC DEUTSCH DT Plug Connectors	 TE Part # CAT-D48-ST273 DEUTSCH Solid Contacts	 TE Part # W8P WEDGE LOCK, 8P, REC, GRN, DT	 TE Part # 1011-027-0805 CLIP, PA66, GRY, 5.08MM HOLE, ST, DT8PIN
 TE Part # CAT-D48-SP729 DEUTSCH Sealing Plugs	 TE Part # CAT-J67-DSCC16 DEUTSCH Size 16 Crimp Contacts	 TE Part # DT-RT1 EXT TOOL, FRONT RELEASE	 TE Part # 2300908-1 0460-003-16329, PIN, SOLID, 20-24AWG, AU
 TE Part # 776364-1 SEALING PLUG, SZ 20 CAVITY	 TE Part # DT8P-L012-GKT GASKET, 8P, BLK, DT/DTM	 TE Part # DT06-08SA-CE03	 TE Part # CAT-D48-SFT273 DEUTSCH Stamped and Formed Contacts

Also in the Series | DEUTSCH DT

 Automotive Connector Caps & Covers (19)	 Automotive Connector Locks & Position Assurance(87)	 Automotive Housings(706)	 Connector Backshells(61)
 Connector Seals & Cavity Plugs(6)	 Connector Strain Relief(28)	 Insertion & Extraction Tools(3)	 Other Automotive Connector Accessories(28)



PCB Headers & Receptacles(106)

Customers Also Bought



TE Part #HD36-24-9SN
PLG, 9P, AL, N, 4/8/12, S



TE Part #DRC16-40SE
PLG, 40P, BLK, E



TE Part #2-1564414-1
Heavy Duty Sealed Connector Series
Housings



TE Part #HDP24-18-14PE-L015
REC, 14P, BLK, E, THD, 16, P




TE Part #163302-8
MATENLOK SOCKET



TE Part #374544-E
STVC 64 M AC VV 4-00 GA06 3,9 * 247
E007



TE Part #DARS24296-000A3
CAR PIN STANDARD CONT. #5, silver
plated



TE Part #1-552296-1
STRAIN RELIEF 64 POS BLACK



TE Part #2-1904025-6
V23234A0004X055-EV-100

Documents

Product Drawings

REC, 8P, GRY, E, XCAP, FLANGE, A

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_DT04-08PA-CL07_99_c-dt04-08pa-cl07-99.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_DT04-08PA-CL07_99_c-dt04-08pa-cl07-99.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_DT04-08PA-CL07_99_c-dt04-08pa-cl07-99.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ICT Terminals and Connectors Catalogue](#)

English

CONNECTOR SELECTOR

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English