

KUMP-11A18-240

✓ ACTIVE

Potter & Brumfield | Potter & Brumfield KUMP

TE Internal #: 6-1393116-4

General Purpose Power Relay, Monostable, 2.9 VA Coil Power Rating AC, 7200 ohm Coil Resistance, Potter & Brumfield KUMP, Power Relays

[View on TE.com >](#)



Relays & Contactors > Relays > Power Relays



Relay Type: **General Purpose Power Relay**
Coil Magnetic System: **Monostable**
Coil Power Rating Class: **[2 – 3 VA]**
Coil Power Rating AC: **2.9 VA**
Coil Resistance: **7200 Ω**

Features

Product Type Features

Relay Type	General Purpose Power Relay
------------	-----------------------------

Configuration Features

Coil Special Features	UL Coil Insulation Class B
Contact Arrangement	2 Form C DPDT-CO
Contact Number of Poles	2

Electrical Characteristics

Insulation Initial Dielectric Between Open Contacts	1200 Vrms
Contact Limiting Making Current	15 A
Contact Limiting Short-Time Current	15 A
Contact Limiting Continuous Current	15 A
Insulation Initial Dielectric Between Adjacent Contacts	2200 Vrms
Insulation Initial Dielectric Between Contacts & Coil	2200 Vrms
Insulation Initial Resistance	100 MΩ
Contact Limiting Breaking Current	15 A
Coil Power Rating AC	2.9 VA
Coil Resistance	7200 Ω
Coil Voltage Rating	240 VAC
Contact Current Rating	15 A



Contact Switching Load (Min)	300mA @ 12V
------------------------------	-------------

Contact Voltage Rating	277 VAC
------------------------	---------

Body Features

Product Weight	85 g[2.988 oz]
----------------	----------------

Contact Features

Contact Material	AgCdO
------------------	-------

Termination Features

Relay Connection Type	Plug-In
-----------------------	---------

Terminal Configuration	Quick Connect Terminals
------------------------	-------------------------

Mechanical Attachment

Product Mount Type	Socket
--------------------	--------

Dimensions

Product Width	35.71 mm[1.4 in]
---------------	------------------

Product Length	38.89 mm[1.53 in]
----------------	-------------------

Product Height	49.2 mm[1.93 in]
----------------	------------------

Usage Conditions

Environmental Category of Protection	RTI
--------------------------------------	-----

Environmental Ambient Temperature (Max)	55 °C[131 °F]
---	---------------

Operating Temperature Range	-45 – 55 °C
-----------------------------	-------------

Operation/Application

Current Type	AC
--------------	----

Coil Magnetic System	Monostable
----------------------	------------

Packaging Features

Packaging Method	Package
------------------	---------

Other

Length Class (Mechanical)	35 – 40 mm
---------------------------	------------

Environmental Ambient Temperature Class	50 – 70 °C
---	------------

Height Class (Mechanical)	40 – 50 mm
---------------------------	------------

Width Class (Mechanical)	30 – 40 mm
--------------------------	------------

	2 – 3 VA
--	----------

Contact Current Class	16 A
-----------------------	------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Cadmium oxide (4.37% in Component Part) Pb (.12% in Component Part) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2-1419106-5 27E893=SOCKET,KU,11,QC,POLY,NA-	 TE Part # 1419106-4 27E046=SOCKET,KU,11,PC,NYL,NAT	 TE Part # 1393143-1 27E043=SOCKET,KU,11,SLG,NYL,N	 TE Part # 1393143-5 27E121=SOCKET,KUP,11,SCW,PLE
--	---	--	---

KUMP-11A18-240

General Purpose Power Relay, Monostable, 2.9 VA Coil Power Rating AC, 7200 ohm
Coil Resistance, Potter & Brumfield KUMP, Power Relays



TE Part # 1393143-2
27E067=SOCKET,KU,11,QC.187,NY

TE Part # 3-1393143-8
27E396=SOCKET,KU,11,SNAP,.187QC

Also in the Series | Potter & Brumfield KUMP

Power Relays(9)

Customers Also Bought

TE Part #CB5025-000
BSTS-11X25-CL/NM

TE Part #49935
DAHT SOLIS 22-10 ASSY

TE Part #6-1393116-2
KUMP-11A18-120=KU

TE Part #1-794611-2
MICRO MNL RPT CNT,LS PC,30AU L

TE Part #31819
SPLICE,SOLIS BUTT 16-14

TE Part #1393143-5
27E121=SOCKET,KUP,11,SCW,PLE

TE Part #2-1879352-9
RR02 5% 4R7 AMMO

TE Part #383760-002
44A0121-24-0/2

TE Part #1-2435260-7
HCP16A, Std Force, 0.187 Term.Smt
Roller

TE Part #2-2435260-0
HCP16A, Lgt Force, 0.250 Term.Smt
Roller



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6-1393116-4_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6-1393116-4_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6-1393116-4_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

KUM-KUMP Series Relay Datasheet

English

KU Sockets & Accessories

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

UL

English