




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.32 – 1.31 mm²**

Mating Tab Width: **4.75 mm [.187 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

|                 |        |
|-----------------|--------|
| Insertion Force | Normal |
|-----------------|--------|

Configuration Features

|                                   |               |
|-----------------------------------|---------------|
| Connection Capacity               | Single        |
| Compatible With Wire & Cable Type | Discrete Wire |

Contact Features

|                                |                  |
|--------------------------------|------------------|
| Quick Disconnect Terminal Type | Receptacle       |
| Mating Tab Width               | 4.75 mm[.187 in] |
| Mating Tab Thickness           | .81 mm[.032 in]  |
| Terminal Orientation           | Straight         |
| Contact Base Material          | Brass            |
| Terminal Plating Material      | Unplated         |
| Crimp Type                     | F-Crimp          |
| Barrel Type                    | Open             |

Termination Features

|  |  |
|--|--|
|  |  |
|--|--|



|                       |              |
|-----------------------|--------------|
| Product Terminates To | Wire & Cable |
|-----------------------|--------------|

Mechanical Attachment

|                         |               |
|-------------------------|---------------|
| Wire Insulation Support | With          |
| Mating Retention Type   | Locking Lance |

Dimensions

|                                      |                               |
|--------------------------------------|-------------------------------|
| Terminal Material Thickness          | .3 mm[.012 in]                |
| Compatible Insulation Diameter Range | 2.31 – 3.3 mm[.091 – .129 in] |
| Wire Size                            | .32 – 1.31 mm <sup>2</sup>    |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Insulation Option           | Uninsulated                |
| Operating Temperature Range | -40 – 110 °C[-40 – 230 °F] |

Packaging Features

|                    |            |
|--------------------|------------|
| Packaging Quantity | 15000      |
| Packaging Method   | Strip/Reel |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JUNE 2024 (241)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                             |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                    |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts


|                                                                                                                                       |                                                                                                                                                       |                                                                                                                                                        |                                                                                                                                                        |
|---------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # 63833-1<br/>FF 187 REC 18-14AWG BR</p> |  <p>TE Part # 2150309-1<br/>OCEAN_2.0_APPLICATOR-E-090F130F-REM</p> |  <p>TE Part # 2150309-2<br/>OCEAN_2.0_APPLICATOR-E-090F130F-REA</p> |  <p>TE Part # 7-2150309-7<br/>OCEAN_2.0_SPARE_PART_KIT-090F130F</p> |
|---------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|

Also in the Series | FASTIN-FASTON 187

|                                                                                                                       |                                                                                                                                 |                                                                                                                    |
|-----------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------|
|  <p>Crimp Terminal Housings(6)</p> |  <p>Insertion &amp; Extraction Tools(1)</p> |  <p>Quick Disconnects(20)</p> |
|-----------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------|

Customers Also Bought

|                                                                                                                                                    |                                                                                                                                                 |                                                                                                                                                        |                                                                                                                                                                 |
|----------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part #5-160558-1<br/>FF 250 REC 0.5-1.5MM2 BR</p>        |  <p>TE Part #1217281-3<br/>FF 110 REC 24-20AWG BR</p>       |  <p>TE Part #534206-2<br/>04 MODII VRT DR CE 100/115</p>          |  <p>TE Part #63833-1<br/>FF 187 REC 18-14AWG BR</p>                        |
|  <p>TE Part #170303-1<br/>FF 250 REC 22-18AWG BR WITH LATCH</p> |  <p>TE Part #4-1618388-6<br/>LEV200A5NAA=RELAY, SPST-NO</p> |  <p>TE Part #5-1618387-7<br/>LEV200A5NAF=RELAY, 24Vdc SPST NO</p> |  <p>TE Part #9-1393030-4<br/>SSRK-240D30 = DIN Rail MOUNT,30A, 240V AC</p> |



Documents

Product Drawings

FF 187 REC 22-16AWG BR

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_62802-1\_Z\_c-62802-1-z.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_62802-1\_Z\_c-62802-1-z.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_62802-1\_Z\_c-62802-1-z.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English