



Connectors > Automotive Connectors > Automotive Connector Accessories > Other Automotive Connector Accessories > DEUTSCH Jiffy Splice



Automotive Connector Accessory Type: **Splice**
Primary Product Material: **VMQ**
Primary Product Color: **Red-Orange**
Operating Temperature Range: **-55 – 125 °C [-67 – 257 °F]**

[All DEUTSCH Jiffy Splice \(2\)](#)

Features

Product Type Features

Automotive Connector Accessory Type	Splice
-------------------------------------	--------

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Primary Product Material	VMQ
Primary Product Color	Red-Orange

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Industry Standards

Compatible With Agency/Standards Products	SAE J2030
---	-----------

Packaging Features

Packaging Quantity	2500
Packaging Method	Box



Other

Serviceable	Yes
-------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-J67-DSCC16
DEUTSCH Size 16 Crimp Contacts



TE Part # CAT-D48-ST273
DEUTSCH Solid Contacts



TE Part # 2300908-1
0460-003-16329, PIN, SOLID, 20-24AWG, AU



TE Part # 0411-291-1405
EXT TOOL, SIZE 16, 14-16 AWG, N, GRN



TE Part # 0411-310-1605
EXT TOOL, SIZE 16, 16-18 AWG, T, LT
BLU

TE Part # 0411-336-1605
EXT TOOL, SIZE 16, 16-20 AWG, E,
DRK BLU

TE Part # CAT-D48-SFT273
DEUTSCH Stamped and Formed
Contacts

TE Part # 1062-14-0177
SOC, SF, SIZE 16, 14-18, SN/SN

Also in the Series | Jiffy Splice

Insertion & Extraction Tools(1)

Other Automotive Connector
Accessories(2)

Customers Also Bought

TE Part #HD36-24-16SN
DEUTSCH HD30 Housings

TE Part #DRC12-70PA
DEUTSCH DRC Housings

TE Part #DT06-08SB-EP06
PLG, 8P, BLK, N, SEAL RET, CAP, B

TE Part #HDC14-3
DUST CAP

TE Part #2273011-3
M8 x 1.0 Angled socket Pigtail

TE Part #929990-1
1,5MM SOCK CONTACT

Documents

Product Drawings
JIFFY SPLICE, Size 16

English

CAD Files
3D PDF

3D



Customer View Model

[ENG_CVM_CVM_JS-16-00_99_c-js-16-00-99.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_JS-16-00_99_c-js-16-00-99.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_JS-16-00_99_c-js-16-00-99.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[CONNECTOR SELECTOR](#)

English

Product Specifications

[Application Specification](#)

English