




Connectors > Terminal Junction Modules & Accessories > Terminal Junction Modules



Terminal Junction System Component Type: **Bussing Module**  
Compatible With Contact Size: **20**  
Number of Positions: **12**  
Sealable: **Yes**  
Contact Current Rating (Max): **7.5 A**

Features

Product Type Features

Connector System	Wire-to-Wire
Terminal Junction System Component Type	Bussing Module
Sealable	Yes

Configuration Features

Number of Positions	12
---------------------	----

Contact Features

Contact Base Material	Copper Alloy
Compatible With Contact Size	20
Contact Current Rating (Max)	7.5 A

Mechanical Attachment

Connector Mounting Type	DIN Rail
-------------------------	----------

Usage Conditions

Operating Temperature Range	-65 – 200 °C[-85 – 392 °F]
-----------------------------	----------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (2.5% in Contact Lead Copper Alloy) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 601966-1  
CRIMPING TOOL M22520/2-01



TE Part # ZPF000000000000569  
020-0511-16

Customers Also Bought



TE Part #65009-001-513  
MODULE ASSY




TE Part #DCR-1A-03  
COMPOSIT RAIL



TE Part #DCR-1A-06  
COMPOSIT RAIL



TE Part #YCTJ120E01BC015000  
ELEC MODULE



TE Part #YCTJ120E04AC015000  
MODULE ASSY




TE Part #YCTJ122E02DC015000  
ELEC MODULE



TE Part #YCTJ122E04FC015000  
ELEC MODULE



TE Part #YCTJ122E05EC015000  
MODULE ASSY



TE Part #YCTD160E01FC015000  
MODULE ASSY



TE Part #YCTJ120E03DC015000  
MODULE ASSY

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_YCTJ120E02CC015000\_99.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_YCTJ120E02CC015000\_99.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_YCTJ120E02CC015000\_99.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.