



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **190**

Centerline (Pitch): **.64 mm [.025 in]**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Receptacle
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Power Positions	5
Number of Columns	95
Stackable	No
Number of Signal Positions	190
PCB Mount Orientation	Vertical
Number of Positions	190
Board-to-Board Configuration	Parallel

Electrical Characteristics



Dielectric Withstanding Voltage (Max)	500 VAC
Insulation Resistance	2 MΩ
Impedance	190 Ω
Operating Voltage	30 VAC

Signal Characteristics

Differential Signaling	Yes
Data Rate	10 Gb/s

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

PCB Contact Termination Area Plating Material Thickness	3.81 – 6.35 μm[149.9997 – 249.9995 μin]
Contact Layout	Inline
PCB Contact Termination Area Plating Material Finish	Matte
Contact Shape & Form	Dual Beam
Contact Mating Area Plating Material Finish	Matte
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Gold
	29.9212 μin
Contact Type	Socket
Contact Current Rating (Max)	11.5 A

Termination Features

Rectangular Termination Post & Tail Thickness	.2 mm[.008 in]
Rectangular Termination Post & Tail Width	.53 mm[.021 in]
Termination Method to PCB	Surface Mount

Mechanical Attachment

PCB Mount Alignment Type	Locating Posts
Mating Retention	Without
Mating Alignment	With
Mating Alignment Type	Polarized
PCB Mount Retention	Without
PCB Mount Alignment	With



Connector Mounting Type	Board Mount
Housing Features	
Centerline (Pitch)	.64 mm[.025 in]
Housing Material	Matte
Dimensions	
Connector Length	76.2 mm[3 in]
Connector Height	15.01 mm[.591 in]
Connector Width	8 mm[.315 in]
Stack Height	9.01 mm, 18 mm, 20 mm, 21.6 mm, 27 mm, 27.8 mm, 29 mm, 31.9 mm[1.255 in]
Usage Conditions	
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
Operation/Application	
Circuit Application	Signal
Industry Standards	
UL Rating	Listed
Compatible With Agency/Standards Products	CSA, UL
Compatible With Approved Standards Products	CSA 1195944, UL E28476
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Quantity	7
Packaging Method	Box, Tube
Product Compliance	
For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free






Solder Process Capability

Reflow solder capable to 260°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 5767006-5 MICT,R/APLUG,190,ASY,.025,.062	 TE Part # 5767039-5 MICTOR,RA PLUG,190,.093PCB,ASY	 TE Part # 1-5767007-2 MICT,260PLUG,190,ASSY,.025,REC	 TE Part # 1-5767005-2 MICT,495PLUG,190,ASSY,.025,REC
 TE Part # 1-5767118-2 MICT,PLG,190,ASY,.025,TAPE PKG	 TE Part # 1-5767119-2 MICT,PLG,190,ASY,.025,TAPE PKG	 TE Part # 1-5767127-2 MICT,PLG,190,ASY,.025,TAPE PKG	 TE Part # 1-5767149-2 MICTOR PLUG ASSY IN TAPE & REE
 TE Part # 5767042-5 MICT,738PLUG,190,ASSY,.025,EXT	 TE Part # 5767056-5 MICT,260,PLUG,190,ASSY,PDNI	 TE Part # 5767082-5 MICT,495,PLUG,190,PDNI,BARBLES	 TE Part # 5767111-5 MICT,PLG,190,ASY,.025 TAPE PKG






TE Part # 5767120-5
[MICT,495PLG,190,ASY,.025,AUPLT](#)



TE Part # 5767127-5
[MICT,REC,190,ASY,.025 TAPE PKG](#)



TE Part # 5767149-5
[MICT,495,PLG,190,TAPE,CAP](#)

Customers Also Bought



TE Part #1-6450530-3
[MBXL R/A HDR 4P+60S+4P](#)



TE Part #2-6450860-1
[MBXLE VERT RCPT 8P + 72S + 8P](#)




TE Part #2057762-3
[IMP100S,H,V3P8C,UG,DEW46,5,5](#)




TE Part #4-1546468-5
[4DB-P107-04=4DB ASSEMBLY Screw Full Thd](#)



TE Part #4-1734531-4
[RCPT,2MM,44P,R ANG MT,8AU,3.ST](#)



TE Part #1879808-6
[RP 1J 37R4 0.1% 15PPM 1K RL](#)



TE Part #5767025-5
[MICTOR .707 PLUG ASSY, 190 POS](#)



TE Part #5767114-9
[MICT,REC,076,ASY,.025,TAPE PKG](#)



TE Part #1-1971818-4
[14P,RAST 2.5 Tab Header,Ex- Locking, THV](#)

Documents

Product Drawings

[MICT,RCPT,190,ASY,GOLD,EXTD](#)

English

CAD Files

[3D PDF](#)

English

[Customer View Model](#)

[ENG_CVM_5767130-5_O.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_5767130-5_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_5767130-5_O.3d_stp.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_5767130-5_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5767130-5_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5767130-5_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[MICTOR Interconnection System](#)

English

[Fine Pitch Stacking Connectors Catalog 889092](#)

English

[Fine Pitch Stacking Connectors - 0.635mm MICTOR Connectors](#)

English

Product Specifications

[Application Specification](#)

English