




Connectors > Contacts > Connector Contacts



Contact Type: **Receptacle**
Contact Mating Area Plating Material: **Tin**
Wire Contact Termination Area Plating Material: **Tin**
Operating Voltage: **600 VDC**

Features

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------

Contact Features

Wire Contact Termination Area Plating Thickness	2.54 µm[100 µin]
Contact Mating Area Plating Material Thickness	2.54 µm[100 µin]
Contact Length	27 mm[1.063 in]
Barrel Type	Open
Contact Type	Receptacle
Contact Mating Area Plating Material	Tin
Wire Contact Termination Area Plating Material	Tin
Contact Retention Within Housing	Without
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	55 A



Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Dimensions

Wire Size	6530 – 10383 CMA
-----------	------------------

Usage Conditions

Operating Temperature Range	0 – 105 °C[32 – 221 °F]
-----------------------------	-------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Compatible With Agency/Standards Products	UL
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	2000
Packaging Method	Strip

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 556136-2
CONT,AMPINNRY WTW,LS PC,10-12

TE Part # 2151317-2
OCEAN_2.0_Applicator-S-180F-RSA

TE Part # 7-2151317-7
OCEAN_2.0_SPARE_PART_KIT-180F

TE Part # 91308-1
EXT TOOL AMP INNERGY WIRE BRD

Customers Also Bought

TE Part #499252-4
050 STRAIN RELIEF A-L RCPT

TE Part #647402-2
02P SL156 HSG W/RMP&TABS,OVSZ

TE Part #1-794954-2
12P RCPT VAL-U-LOK V2

TE Part #53894-4
HSG ASSY,PWR LK,SRS1,1 POS,RED

TE Part #770018-1
03P UMNLII IN-LNE PLUG HSG KIT

TE Part #1-770004-0
UMNL II SOK SN/AUNI/PHBZ

TE Part #ANT-433-HESM
Antenna 1/4 Wave Coil 433MHz SMT

TE Part #1-1633923-1
ANVIL, COMBINATION

TE Part #OTX-433-HH-KF1-HT
Remote HT 433MHz OOK AM 1Btn KF TX EU

TE Part #OTX-433-HH-KF2-MS
Remote MS 433MHz OOK AM 2Btn KF TX EU

Documents

Product Drawings



CONT,AMPINNRGY WTW,STRIP,10-12

English

CAD Files

Customer View Model

ENG_CVM_556136-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_556136-1_A.3d_stp.zip

English

Customer View Model

ENG_CVM_556136-1_A.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

POWER_CONNECTORS_CATALOG_SEC02_CABLE_MOUNTED

English

1654742_HOUSEHOLD_APPLIANCES_RAST5

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Inspection of AMPINNERGY System Power Contacts

English