

DTP06-2S ✓ ACTIVE

DEUTSCH | DEUTSCH DT, DEUTSCH DTP

TE Internal #: DTP06-2S

Housing for Female Terminals, Wire-to-Wire, 2 Position, 6.7 mm [.264 in] Centerline, Sealable, Gray, Wire & Cable, Power, Hybrid

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings > DEUTSCH DTP Housings



Connector System: **Wire-to-Wire**

Number of Positions: **2**

Connector & Housing Type: **Housing for Female Terminals**

Centerline (Pitch): **6.7 mm [.264 in]**

Sealable: **Yes**

[All DEUTSCH DTP Housings \(34\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector System	Wire-to-Wire
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Integrated in Housing

Configuration Features

Blank Cavity Position	0
Connector Seal Code	N Seal
Number of Positions	2
Number of Rows	1

Electrical Characteristics



Operating Voltage	200 VAC
-------------------	---------

Nominal Voltage Architecture	200 V
------------------------------	-------

Body Features

Cable Exit Angle	180°
------------------	------

Primary Product Color	Gray
-----------------------	------

Contact Features

Contact Size	Size 12
--------------	---------

Contact Type	Socket
--------------	--------

Mating Pin Diameter	2.4 mm[.094 in]
---------------------	-----------------

Contact Current Rating (Max)	25 A
------------------------------	------

Mechanical Attachment

Terminal Position Assurance	No
-----------------------------	----

Strain Relief	Without
---------------	---------

Mating Alignment Type	Polarized
-----------------------	-----------

Mating Alignment	With
------------------	------

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Housing Material	PA GF
------------------	-------

Centerline (Pitch)	6.7 mm[.264 in]
--------------------	-----------------

Dimensions

Connector Height	34.6 mm[1.36 in]
------------------	------------------

Product Width	18.6 mm[.732 in]
---------------	------------------

Product Length	18.6 mm[.732 in]
----------------	------------------

Compatible Insulation Diameter Range	3.4 – 4.9 mm[.134 – 1.95 in]
--------------------------------------	------------------------------

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
-----------------------------	----------------

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Degree of Protection	IP68, IP6K9K
----------------------	--------------

Compatible With Agency/Standards Products	SAE J2030
---	-----------



UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # CAT-D48-SP729
DEUTSCH Sealing Plugs



TE Part # CAT-D486-CH8172
DEUTSCH DTP Housings



TE Part # CAT-D48-ST273
DEUTSCH Solid Contacts



TE Part # WP-2S
WEDGE LOCK, 2P, PLG, ORG, DTP



TE Part # DT-RT1
EXT TOOL, FRONT RELEASE



TE Part # 1062-12-0144
SOC, SF, SIZE 12, 12-14, AU/SN



TE Part # 1062-12-0222
SOC, SF, SIZE 12, 10, NI/NI



TE Part # DTP2S-BT
BOOT, 2P, PLG, ST, GRY




TE Part # 1062-12-0166
SOC, SF, SIZE 12, 12-14, NI/SN



TE Part # 1062-12-0244
SOC, SF, SIZE 12, 10, AU/SN


Also in the Series | **DEUTSCH DT**




Automotive Connector Caps & Covers
(19)




Automotive Connector Locks &
Position Assurance(87)



Automotive Housings(706)




Connector Backshells(61)




Connector Seals & Cavity Plugs(6)




Connector Strain Relief(28)



Insertion & Extraction Tools(3)




Other Automotive Connector
Accessories(28)



PCB Headers & Receptacles(106)

Also in the Series | DEUTSCH DTP



Automotive Connector Locks & Position Assurance(4)




Automotive Housings(34)



Connector Backshells(1)



Insertion & Extraction Tools(3)



PCB Headers & Receptacles(5)

Customers Also Bought



TE Part #DTP06-4S
DEUTSCH DTP Housings



TE Part #WP-2S
DEUTSCH DTP Wedgelocks



TE Part #W4S-ZZ
WEDGE LOCK, 4P, PLG, ORG, STD, DT



TE Part #DT06-2S
DEUTSCH DT Plug Connectors



TE Part #0462-203-12141
SOC, SOLID, SIZE 12, 12-14AWG, NI



Documents

Product Drawings

[PLG, 2P, GRY, N](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_DTP06-2S_99_c-dtp06-2s-99.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_DTP06-2S_99_c-dtp06-2s-99.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_DTP06-2S_99_c-dtp06-2s-99.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ICT Terminals and Connectors Catalogue](#)

English

[CONNECTOR SELECTOR](#)

English

Product Specifications

[Engineering Report](#)

English

Agency Approvals

[UL Report](#)

English