



Terminals & Splices > PCB Terminals



PCB Terminal Type: **Tab**
Mating Tab Width: **6.35 mm [.25 in]**
Mating Tab Thickness: **.81 mm [.032 in]**
PCB Hole Diameter: **4.5 mm [.177 in]**
Termination Method to PCB: **Through Hole - Screw**

Features

Product Type Features

Terminal Features	Stud Hole
Insertion Force	Normal

Contact Features

Terminal Plating Finish	Matte
PCB Contact Termination Area Plating Material Thickness	1.01 μm[40 μin]
Contact Mating Area Plating Material Thickness	1.01 μm[40 μin]
PCB Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Plating Material	Tin
Contact Underplating Material	None
Terminal Size	6.35
Terminal Orientation	Straight

Termination Features



Termination Method to PCB	Through Hole - Screw
Product Terminates To	Printed Circuit Board

Dimensions

Stud Diameter	4.5 mm[.177 in]
PCB Hole Diameter	4.5 mm[.177 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 181948-2 250 FASTON,TAB,TPBR	 TE Part # 42802-1 250 FASTON TAB TPBR	 TE Part # 41480 250 FASTON TAB TPBR	 TE Part # 42117-2 250 FASTON TAB TPBR
 TE Part # 61499-1 250 FASTON TAB TPBR	 TE Part # 61365-1 250 FASTON TAB TPBR	 TE Part # 181949-2 250 FASTON,TAB,TPBR	 TE Part # 62627-2 250 FASTON TAB BR
 TE Part # 62627-1 250 FASTON TAB TPST	 TE Part # 63274-1 250 FASTON TAB BR	 TE Part # 1217002-1 250 FASTON,TAB, NPCST	 TE Part # 42095-1 250 FASTON TAB TPBR
 TE Part # 63971-1 250 FASTON TAB TPBR	 TE Part # 60080-2 250 FASTON TAB TPBR	 TE Part # 62627-3 250 FASTON TAB BR	 TE Part # 160650-2 250 FASTON,PCB TAB,TNBR





TE Part # 140736-2
250 FASTON,TAB,TPBR



TE Part # 63274-3
250 FASTON TAB BR

Also in the Series | FASTON 250



Compression Connectors(4)



Crimp Terminal Housings(132)



Insertion & Extraction Tools(6)



Magnet Wire Terminals(1)



PCB Terminals(134)



Quick Disconnects(426)



Splices(4)


Customers Also Bought



TE Part #1393779-5
V23101D 3A201



TE Part #41333
RING 18-14 AWG TPBR



TE Part #2-87195-5
MOD IV RECP LP



TE Part #4-640426-1
11P MTA156 CONN ASSY 18AWG
ORA



TE Part #342145-1
16-14 F.E.P.G. RING TONGUE NO.





TE Part #NB14354001
VERSAFIT-3/4-0-FSP



TE Part #5504008-3
CONN KIT,STC,125UM MM, 3mm



TE Part #3580590030
TRSA-1019/C/1/F



Documents

Product Drawings

250 FASTON TAB TPBR

English

CAD Files

Customer View Model

ENG_CVM_CVM_63038-1_J.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_63038-1_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_63038-1_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FASTON Tabs

English

Product Specifications

Application Specification

English