

FAIRCHILD

SEMICONDUCTOR

日本語 한국어 简体中文

Search:

Google

DATASHEETS, SAMPLES, BUY

TECHNICAL INFORMATION

APPLICATIONS

DESIGN CENTER

SUPPORT

COMPANY

INVESTORS

MY FAIRCHILD

Home >> Find products

KS3302BU

NPN/45V/200MA

Other Links

[Product Folder](#)

This page

[Bookmark this page](#)

[Print version](#)

Qualification Data

[Fairchild Product Reliability Report](#)

Contact your regional quality and reliability [representative](#) with any questions on product qualification support.

Test Standards:

- Moisture Sensitivity: NA
- Physical Dimensions: TO-92

[back to top](#)

Related Links

[Request samples](#)

[How to order products](#)

[Product Change Notices \(PCNs\)](#)

[Support](#)

[Sales support](#)

[Quality and reliability](#)

[Design center](#)

Attribute	Value
General Information	
Device Marking(TOP MARK)	KS 3302 -&3
Family Code	0S2
Package Type	TO-92
Package Description	3 LD PLASTIC PKG (APK=AM)
Pin Count	3
FIT	9.2
Maximum Reflow Temperature	NA (thru hole)
MSL Rating	NA (thru hole)
Restriction of Hazardous Substance	
Standard Plating Finish	Matte Sn
Base Metal/Leadframe Material	Copper,Iron,Phosphorus,Silver

Lead Pitch	1270
Minimum Lead Spacing	810
Die Fabrication	
Fabrication Process Identifier	DB0815A
Package Assembly*	
Plating Finish Layer Thickness	8.0um - 18um
Moisture Sensitivity	NA

*If an attribute is listed twice, either can be used on the part.

[back to top](#)



[Products](#) | [Design Center](#) | [Support](#) | [Company News](#) | [Investors](#) | [My Fairchild](#) | [Contact Us](#) | [Site Index](#) | [Privacy Policy](#) | [Site Terms & Conditions](#) | [Standard Terms & Conditions of Sale](#)

© 2006 Fairchild Semiconductor