

EDS06SNRSTR04Q

✓ ACTIVE

Alcoswitch | Alcoswitch DIP EDS


TE Internal #: 7-2319848-9

Gold Flash, Black, High Temperature Nylon, Sealed Device, 6 Switch, -20 – 85 °C, DIP, Slide Actuator Style, Alcoswitch DIP EDS, DIP & SIP Switches

[View on TE.com >](#)



Switches > DIP & SIP Switches



Switch Contact Plating Material: Gold Flash

Case Color: Black

Case Material: High Temperature Nylon

Sealed Device: Yes

Number of Switches: 6

Features

Product Type Features

Sealed Device	Yes
DIP & SIP Switch Type	DIP
Actuator Style	Slide

Configuration Features

Number of Positions	6
Number of Switches	6
Configuration (Pole-Throw)	Single Pole - Single Throw

Electrical Characteristics

Contact Current Rating	.025 A
Operating Voltage	24 VDC

Body Features

Actuator Color	White
Sealing Method	Sealing Tape
Product Orientation	Vertical



Case Color	Black
Case Material	High Temperature Nylon

Contact Features

Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Gold Flash
Switch Contact Plating Material	Gold Flash
Contact Base Material	Copper Alloy

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Product Length	15.14 mm[.596 in]
Product Height	3.45 mm[.136 in]

Usage Conditions

Operating Temperature Range	-20 – 85 °C
-----------------------------	-------------

Packaging Features

Packaging Quantity	900
Packaging Method	Tape & Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 6-2319848-4
END STACK DIP1PGRECESSSEALT&R



TE Part # 4-2319848-5
END STACK DIP 3P G RECESS T&R



TE Part # 6-2319848-7
END STACK DIP 4P G RECESS SEAL T&R



TE Part # 6-2319848-8
END STACK DIP 5P G RECESS SEAL T&R




TE Part # 1-2319847-0
END STACK DIP 10P G RAISED TUBE



TE Part # 7-2319848-8
END STACK DIP 5P J RECESS SEAL T&R

Also in the Series | Alcoswitch DIP EDS



DIP & SIP Switches(121)

Customers Also Bought



TE Part #2102736-1
BP, Center, MULTIGIG RT 2R

TE Part #2102737-1
BP, Right End, MULTIGIG RT 2R

TE Part #1676298-2
RN 0805 301R 0.1% 10PPM 1KRL

TE Part #969973-2
2x2P HV100 REC. CON, SMD, GOLD, BLISTER

TE Part #1676414-2
RN 0805 6K19 0.1% 10PPM 1KRL

TE Part #1-1625812-2
3631B 47UH 15% FIO

TE Part #4-2176091-7
RP 2A 0.25W 174R 0.1% 25PPM 1K RL

TE Part #1977831-3
DIP SWITCH GDH06SATR04

Documents

Product Drawings

END STACK DIP 6P J RECESS SEAL T&R

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-2319848-9_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-2319848-9_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-2319848-9_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English