



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **20**

Centerline (Pitch): **2.54 mm [.1 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	20
Number of Rows	2

Electrical Characteristics

Termination Resistance	12 mΩ
Insulation Resistance	5000 MΩ
Dielectric Withstanding Voltage (Max)	750 V
Operating Voltage	250 VAC

Body Features

Primary Product Color	Black
-----------------------	-------



Contact Features

Contact Type	Socket
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	3 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	With
Mating Retention Type	Detent Latching
Mating Retention	With

Housing Features

Housing Entry Configuration	Both Ends Closed
Housing Material	Nylon - GF
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Connector Length	25.4 mm[1 in]
Connector Height	6.1 mm[.24 in]
Row-to-Row Spacing	2.54 mm[.1 in]

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
Compatible With Approved Standards Products	CSA LR7189, UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 103168-8
20 MODII HDR DRST SHRD .100CL

TE Part # 87666-2
MOD IV RECP PLTD 30 SEL

TE Part # 6-87756-7
MOD IV REC STP INT'L SPEC REEL

TE Part # 87756-6
MOD IV RECP PLTD SN











TE Part # 2-87195-4
MOD IV RECP PLTE 15 DPLX

TE Part # 87809-1
MOD V RECP PLTD 30 AU




TE Part # 6-87756-2
MOD IV RECP PLTD 15 DPLX LF


TE Part # 87309-9
MOD V RECP PLTD 30 AU



 TE Part # 102917-5 MOD IV RECP PLTD 15 SEL	 TE Part # 87523-5 MOD IV RECP PLTD SN	 TE Part # 102548-5 MOD IV RECP PLTD 30 SEL	 TE Part # 87309-8 MOD V RECP PLTD SN
 TE Part # 2-87523-3 MOD IV RECP PLTD 15 DPLX	 TE Part # 5-103171-4 MOD IV RECP PLTD 30 DPLX LF	 TE Part # 85969-8 MOD IV RECP PLTD 30 SEL	 TE Part # 87666-3 MOD IV RECP PLTD SN
 TE Part # 102618-8 20 MODII HDR DRST SHRD .100CL	 TE Part # 103169-8 20 MODII HDR DRST SHRD .100CL	 TE Part # 5-102920-1 MOD IV RECP PLTD 30 DPLX LF	 TE Part # 103455-1 MOD V RECP PLTD 30 AU

Also in the Series | AMPMODU IV/V

 Backplane Connector Housings(1)	 Connector Caps & Covers(15)	 Connector Contacts(321)	 Connector Hardware(13)
 Insertion & Extraction Tools(4)	 PCB Headers & Receptacles(931)	 Rectangular Connector Housings(5)	 Standard Rectangular Connectors(7)



Customers Also Bought

Documents

Product Drawings
20 MODIV HSG W/STR RLF DR MRKD
English

CAD Files
3D PDF
English
Customer View Model
ENG_CVM_87733-1_G1.3d_igs.zip
English
Customer View Model
ENG_CVM_87733-1_G1.3d_stp.zip
English
Customer View Model
ENG_CVM_87733-1_G1.2d_dxf.zip
English
3D PDF



3D

Customer View Model

[ENG_CVM_CVM_87733-1_M.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_87733-1_M.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_87733-1_M.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPMODU_INTERCONNECTION_SYSTEM_SECTION5_CONT](#)

English

Product Specifications

[Product Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[AMPMODU MOD IV RECEPTACLE CONNECTORS \(WITH STRAIN RELIEF TABS\)](#)

English

Agency Approvals

[UL](#)

English