




Positive Lock | Mark II, Positive Lock 187

TE Internal #: 63407-2

Receptacle, 24 – 20 AWG Wire Size, .2 – .51 mm² Wire Size, Mating
Tab Width 4.75 mm [.187 in], Straight, Brass, Positive Lock 187,
Quick Disconnects

[View on TE.com >](#)

Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.2 – .51 mm²**

Mating Tab Width: **4.75 mm [.187 in]**

Mating Tab Thickness: **.51 mm [.02 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Pre-Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------



Mechanical Attachment

Extraction Force	7 – 100 Newton
Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Terminal Material Thickness	.3 mm[.012 in]
Product Length	19.18 mm[.755 in]
Compatible Insulation Diameter Range	1.52 – 2.8 mm[.06 – .11 in]
Wire Size	.2 – .51 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Packaging Features

Packaging Quantity	12000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as



EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 63784-1
RCPT POS/LK 187 0126PTPBR

TE Part # 2836300-2
OCEAN-2.0-APPLICATOR-S-070F140F-RSA

TE Part # 7-2836300-7
OCEAN_2.0_SPARE_PART_KIT-070F140F

Also in the Series | Mark II

Automotive Connector Locks & Position Assurance(1)

Automotive Housings(16)

Automotive Terminals(11)

Connector Seals & Cavity Plugs(1)

Crimp Terminal Housings(76)

Insertion & Extraction Tools(2)

Other Automotive Connector Accessories(2)

Quick Disconnects(57)

Also in the Series | Positive Lock 187



Crimp Terminal Housings(86)



Insertion & Extraction Tools(2)




Insulation Boots & Sleeves(7)



Quick Disconnects(57)

Customers Also Bought



TE Part #1217861-1
250 FASTON,PCB TAB,TCBR



TE Part #1217095-2
RCPT 250 POS-LOCK 16-12 TPBR



TE Part #42801-2
187 FASTON REC 20-16 AWG TPBR



TE Part #1217095-1
RCPT 250 POS-LOCK 16-12 0126BR



TE Part #63854-1
250 PL MKIII REC. 18-14AWG BR



TE Part #828904-2
SINGLE WIRE SEAL FOR J.P.T.CON



TE Part #7-1452668-1
MCON 1.2 LL REC SWS SN



TE Part #60634-1
FF 250 REC 18-14AWG BR

Documents

Product Drawings

PL 187 TERMINAL REC 0.2-0.5 MM2 PTPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_63407-2_AD.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_63407-2_AD.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_63407-2_AD.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

Positive Lock Receptacles

English

Product Specifications

Application Specification

English