

BEGA861NN0000150A000

✓ ACTIVE

TE Internal #: BEA861N0000150A000

Cable-to-Panel, Power, Panel Mount, Electrodeposited Nickel, Zinc Alloy, PBT GF, Size 17, Shielded, Receptacle, Standard Circular Connectors

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Cable-to-Panel**

Connector Mounting Type: **Panel Mount**

Sealable: **No**

Circuit Application: **Power**

Shell Plating Material: **Electrodeposited Nickel**

Features

Product Type Features

Product Type	Connector Assembly
Connector System	Cable-to-Panel
Sealable	No
Circular Connector Type	Receptacle
Shell Type	Metal

Electrical Characteristics

Operating Voltage	630 VAC
-------------------	---------

Body Features

Environmental Protection	IP67
Shell Plating Material	Electrodeposited Nickel
Shell Base Material	Zinc Alloy
Circular Connector Insulation Material Type	PBT GF

Mechanical Attachment

Mating Retention Type	Speedtec (Triple Start Threaded)
-----------------------	----------------------------------



Panel Mount Feature Type	Flange with Mounting Holes
Connector Mounting Type	Panel Mount

Housing Features

Circular Connector Shell Size	17
Alignment Keyed	0°

Usage Conditions

Operating Temperature Range	-20 – 130 °C[-4 – 266 °F]
-----------------------------	---------------------------

Operation/Application

Durability Rating	500 Cycles
Circuit Application	Power
Shielded	Yes

Industry Standards

UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (3% in Component part) <small>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous




materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # BSA863N0086201A000
917 PLUG




TE Part # C0-0003-000-000
POSITIONING INSERT FOR 1 MM CONTACTS



TE Part # C0-0235-000-P00
DIGITAL CRIMPING TOOL, SMALL




TE Part # C0-0101-000-P00
CRIMPING TOOL SMALL WITH POSITIONER




TE Part # C0-0201-000-P00
CRIMPING TOOL MID-SIZE


Customers Also Bought




TE Part #AKA020N00400100000
623 EXTENSION, SPEEDTEC




TE Part #ASA021N00400100000
623 PLUG, SPEEDTEC




TE Part #ASA021N00400235000
623 PLUG




TE Part #ASA021N00700235042
623 PLUG, DELIVERY AS INDIVIDUAL PARTS




TE Part #CSA263N00440001000
940 PLUG



TE Part #EGA002N00000600000
615 ITEC RECEPTACLE, ANGLED



TE Part #EEA002N000000004000
615 ITEC RECEPTACLE



TE Part #AKA021N00730255000
623 EXTENSION, SPEEDTEC-READY

Documents

- CAD Files
- 3D PDF



3D

Customer View Model

[ENG_CVM_CVM_BEA861N0000150A000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_BEA861N0000150A000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_BEA861N0000150A000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[BEA861N0000150A000](#)

English

[fuer Datenblaetter, die online konfigurierbar sind](#)

German

Product Specifications

German