

ROX9J110K

✓ ACTIVE

Neohm | Neohm ROX

TE Internal #: 8-2176416-1

General Purpose Resistor, Metal Oxide Film, 9 W, 110K ohm, 5 %, ±350 ppm/°C, Axial-Leaded, Copper Termination, 54 x 8.5 mm, Box, Neohm ROX

[View on TE.com >](#)



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: General Purpose Resistor

Element Type: Metal Oxide Film

Power Rating: 9 W

Resistance Class: 1kΩ – 1MΩ

Resistance Value: 110K Ω

Features

Product Type Features

Resistor Type	General Purpose Resistor
Element Type	Metal Oxide Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	750 V
Power Rating	9 W
Resistance Class	1kΩ – 1MΩ
Resistance Value	110K Ω
Passive Component Tolerance	5 %

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

--	--



Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	54 x 8.5 mm
------------------------------	-------------

Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±350 ppm/°C

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

ROX9J110K

General Purpose Resistor, Metal Oxide Film, 9 W, 110K ohm, 5 %, ±350 ppm/°C, Axial-Leaded, Copper Termination, 54 x 8.5 mm, Box, Neohm ROX



TE Part # 2-1625892-1
3W SM M/OX 5% 1K0

TE Part # 4-1625886-1
1W SM M/OX 5% 820K

TE Part # 6-1676123-7
1/2W SM M/OX 5% 470R

TE Part # 1625881-2
1W STD M/OX 2% 220R

TE Part # 1625893-5
5W SM M/OX 5% 47K

Also in the Series | Neohm ROX

Through-Hole Resistors(798)

Customers Also Bought

TE Part #1658607-1
50 POS HDF PLUG, MS, LEAD FREE

TE Part #1-2176070-3
3521 33R 1% 2W

TE Part #9-2176231-8
SMD Power Resistor: 3 Watt, 1% Tol

TE Part #4-1879355-0
RR03 5% 180K AMMO

TE Part #1625893-6
5W SM M/OX 5% 150K

TE Part #9-2176412-7
5W XSM M/OX 5% 51K

TE Part #9-2176414-4
7W STD M/OX 5% 150K

TE Part #8-2176415-7
8W STD M/OX 5% 110K



Documents

Product Drawings

9W STD M/OX 5% 110K

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_8-2176416-1_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_8-2176416-1_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_8-2176416-1_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Flame Proof Power Metal Oxide Film Resistors - Type ROX Series - Tyco Electronics Passives

English