

**CIRPSE06T2214SVON**

x OBSOLETE

TE Internal #: Y5015-000000005391

TE Internal Description: FREE SOCKET CONNECTOR

Plug with RFI Grounding - Female - CIRP

[View on TE.com >](#)

Connectors &gt; Circular Connectors &gt; Standard Circular Connectors &gt; Plug with RFI Grounding - Female - CIRP

Connector System: **Cable-to-Cable, Wire-to-Wire**Number of Positions: **19**Connector & Contact Terminates To: **Wire & Cable**Circuit Application: **Power & Signal**Reverse Gender: **Yes**

## Features

### Product Type Features

Product Type	Connector Assembly
Accessory Color	Black
Prewired	No
Connector System	Cable-to-Cable, Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Receptacle
Shell Type	Metal

### Configuration Features

Factory Installed Backshell	Without
Number of Positions	19
Contacts Preloaded	No

### Electrical Characteristics

Operating Voltage	700 VAC
-------------------	---------

### Body Features

Shell Plating Material	Black Chromate Over Zn Cobalt
Shell Base Material	Aluminum Alloy
Circular Connector Insulation Material Type	Low Fire Hazard Thermoplastic

### Contact Features

Reverse Gender	Yes
Contact Layout Arrangement	Circular
Circular Connector Contact Type	Socket

#### Mechanical Attachment

Mating Retention Type	Bayonet
Mating Alignment	With
Mating Alignment Type	Keyed
Mating Retention	With

#### Housing Features

Circular Connector Shell Size	22
-------------------------------	----

#### Usage Conditions

IP Water Sealing Level	IP67
Operating Temperature Range	-55 – 125 °C [-67 – 257 °F]

#### Operation/Application

Circuit Application	Power & Signal
Shielded	Yes

#### Packaging Features

Packaging Quantity	10
--------------------	----

#### Other

Position Locations Omitted	All
Field Serviceable	Yes

#### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (.15% in Aluminium alloy component)
	Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

## Halogen Content

Not Yet Reviewed for halogen content

## Solder Process Capability

Not applicable for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Customers Also Bought



TE Part #DT04-12PB-BL04  
REC, 12P, BLK, N, ENH KEY, FLANGE, B



TE Part #175217-2  
DYNAMIC REC CONTACT M L/P



TE Part #322798  
SOLIS R HR 22-16COM 22-18MIL 8




TE Part #4426612006  
RAYRIM-NR9-0-STK



TE Part #51863  
PIDG Ring Tongue Terminals



TE Part #E76198-000  
HX-SCE-38.1-50-4



TE Part #59824-1  
TETRA-CRIMP PIDG PG FASTON 22-10 ASSY



TE Part #270225-000  
B-150-07



TE Part #2255146-1  
MINI SAHT D3000-M

## Documents

## Product Drawings

FREE SOCKET CONNECTOR

French

---

[Datasheets & Catalog Pages](#)

[CIRP Catalog](#)

[CIRP Catalog](#)

English

---

[Product Specifications](#)

[Application Specification](#)

French