




EMI & EMC Solutions > EMI Filters > Power Line Filters > 3-Phase Filters > 3 Phase Filters, Corcom AYA Series



Current Rating: 36 A

Input Termination Type: Threaded Bolt

Output Termination Type: Threaded Bolt

Wiring Configuration: WYE (4 wire + ground)

Operating Voltage: 440 VAC

[All 3 Phase Filters, Corcom AYA Series \(0\)](#)

Features

Product Type Features

Filtering Requirements	Filtered
Input Termination Type	Threaded Bolt
Output Termination Type	Threaded Bolt

Configuration Features

Wiring Configuration	WYE (4 wire + ground)
----------------------	-----------------------

Electrical Characteristics

Current Rating	36 A
Operating Voltage	440 VAC

Mechanical Attachment

Product Mount Type	Chassis
--------------------	---------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C8114-A11
EMI Filter Accessories, Corcom A Series



TE Part # CAT-C8114-AY61
3 Phase Filters, Corcom AYO Series

Also in the Series |

Customers Also Bought




TE Part #5039244037
DR-25-1-0-SP



TE Part #4-1419111-2
PT270024



TE Part #6-1415034-1
PT78720




TE Part #120411-000
B-040-24-N



TE Part #5-1419111-9
PT28800



TE Part #280359
AMPMODU II REC. HSG, SINGLE ROW, 4 POS.



TE Part #182206-2
MOD 2 TERMINAL



TE Part #9-1609968-9
KEP 30A 1S HIGH PLUS SP BS WYE 440 VAC

Documents

Product Drawings

36AYA6 ARY=F7747

English

CAD Files

Customer View Model

ENG_CVM_CVM_6609068-5_A.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_6609068-5_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6609068-5_A.3d_igs.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654001_Corcom_Product_Guide_AYA_Series

English

Datasheet - Ev-Charging Passives

English

1-1654250-1_CORCOM_EMI_RFI_QRG

English

Agency Approvals



UL Report

English