




Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**
Connector & Housing Type: **Plug**
Connector System: **Wire-to-Board**
Number of Positions: **6**
Centerline (Pitch): **11.18 mm [.44 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	6
Number of Power Positions	6
Number of Signal Positions	0
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------

Contact Features

Contact Current Rating (Max)	35 A
------------------------------	------



Contact Retention Within Housing	With
Contact Type	Receptacle

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Retention	With
Mating Alignment	With
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention Type	Latch

Housing Features

Centerline (Pitch)	11.18 mm[.44 in]
Housing Color	Black
Housing Material	Polycarbonate

Dimensions

Connector Height	9.4 mm[.37 in]
Product Width	36.58 mm[1.44 in]
Product Length	75.18 mm[2.96 in]
Compatible Insulation Diameter Range	1.02 – 25.91 mm[.04 – 1.02 in]
Wire Size	1600.53 – 12066.13 CMA

Usage Conditions

Operating Temperature Range	0 – 105 °C[32 – 221 °F]
-----------------------------	-------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

CSA Rating	Certified, LR 7189
UL Rating	Recognized
Compatible With Agency/Standards Products	CSA, UL
Compatible With Approved Standards Products	UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Loose Piece
------------------	-------------



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 556881-6
RCPT ASY,VRT,AMPINRGY WTB,6POS





TE Part # 556882-6
RCPT ASY,R/A,AMPINRGY WTB,6POS



TE Part # 91308-1
EXT TOOL AMP INNERGY WIRE BRD

Customers Also Bought



 TE Part #DT04-08PC REC, 8P, GRN, N, C	 TE Part #1-770985-0 MINI UMNL PIN 26-22AWG AU LP	 TE Part #1-172159-2 MINI UNIVERSAL M-N-L CAP 4P	 TE Part #172343-1 MINI UNIVERSAL M-N-L HOUSING
 TE Part #1-172167-9 4 POS SR MINI UNIV	 TE Part #1-172159-9 MINI UNIVERSAL M-N-L CAP 4P	 TE Part #5-530519-2 HIGH CURRENT CONT-STRIP	 TE Part #1-172167-2 4 POS DR MINI UNIV
 TE Part #318900-1 CONTROL BOX ASSY(MAN ADJ BNCH)			

Documents

Product Drawings

PLUG HSG,AMPINNERGY WTB,6 POS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_556879-6_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_556879-6_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_556879-6_E.3d_stp.zip

English

3D PDF

English



Customer View Model

[ENG_CVM_556879-6_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_556879-6_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_556879-6_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[POWER_CONNECTORS_CATALOG_SEC02_CABLE_MOUNTED](#)

English

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English

Product Specifications

[Application Specification](#)

English

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[Agency Approval Document](#)

English