



Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Cable-to-Cable**

Connector Mounting Type: **Cable Mount (Free-Hanging)**

Number of Positions: **17**

Sealable: **No**

Circuit Application: **Signal**

Features

Product Type Features

Product Type	Connector Assembly
Connector System	Cable-to-Cable
Sealable	No
Circular Connector Type	Plug
Shell Type	Metal

Configuration Features

Number of Positions	17
Number of Signal Positions	17

Electrical Characteristics

Operating Voltage	63 VAC
-------------------	--------

Body Features

Environmental Protection	IP67
Shell Plating Material	Electrodeposited Nickel
Shell Base Material	Zinc Alloy



Circular Connector Insulation Material Type

PBT GF

Mechanical Attachment

Panel Mount Feature Type	Screw Mount
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Circular Connector Shell Size	17
-------------------------------	----

Dimensions

Cable Diameter Range	9.5 – 12 mm[.37 – .47 in]
----------------------	---------------------------

Usage Conditions

Operating Temperature Range	-20 – 130 °C[-4 – 266 °F]
-----------------------------	---------------------------

Operation/Application

Durability Rating	500 Cycles
Circuit Application	Signal
Shielded	Yes

Industry Standards

UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (3.5% in Component part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # AGC874N0000150A000
617 RECEPTACLE ANGLED
ROTATABLE




TE Part # AGC874N0000151A000
617 RECEPTACLE ANGLED
ROTATABLE




TE Part # AEA874N0000150A000
617 RECEPTACLE, SPEEDTEC-READY



TE Part # 50-0086-000-P00
617/917 CABLE CLAMP, CROWN



TE Part # C0-0235-000-P00
DIGITAL CRIMPING TOOL, SMALL



TE Part # C0-0231-000-P00
CRIMPING TOOL SMALL

Customers Also Bought



TE Part #ASA021N00100235000
623 PLUG



TE Part #ASA021N00410100000
623 PLUG, SPEEDTEC



TE Part #BKA199N00580203000
923 EXTENSION, SPEEDTEC-READY



TE Part #BSA078N00420235000
923 PLUG





TE Part #BSA108N00420236000
923 PLUG, SHORT



TE Part #AKA874N0086151A000
617 EXTENSION, SPEEDTEC-READY



TE Part #A2-0043-001-000
923 CLAMPING RING ADAPTER



TE Part #BGC878N0000151A000
917 RECEPTACLE, ANGLED, ROTATABLE

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_ASA876N0086200A000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_ASA876N0086200A000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_ASA876N0086200A000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ASA876N0086200A000

English

fuer Datenblaetter, die online konfigurierbar sind

German