

AOW125A60/AOWF125A60

600V, α MOS5 TM N-Channel Power Transistor

General Description

- Proprietary $\alpha MOS5^{TM}$ technology
- Low R_{DS(ON)}
- Optimized switching parameters for better EMI performance
- Enhanced body diode for robustness and fast reverse recovery

Applications

- SMPS with PFC, Flyback and LLC topologies Micro inverter with DC/AC inverter topology


Product Summary

V_{DS} @ T_{i,max} 700V 100A I_{DM} $R_{\text{DS}(\text{ON}),\text{max}}$ < 0.125Ω 39nC $\mathbf{Q}_{g,typ}$

E_{oss} @ 400V 6.3µJ

100% UIS Tested 100% R_g Tested





Orderable Part Number	Package Type	Form	Minimum Order Quantity
AOW125A60	TO262	Tube	1000
AOWF125A60	TO262F	Tube	1000

Absolute Maximum Ratings T_A=25°C unless otherwise noted

Parameter		Symbol	AOW125A60	AOWF125A60	Units
Drain-Source Voltage		V_{DS}	600		V
Gate-Source Voltage		V_{GS}	±20		V
Continuous Drain	T _C =25°C		28	28*	
Current	T _C =100°C	I _D	18	18*	Α
Pulsed Drain Current ^C		I _{DM}	100		
Avalanche Current ^C	L=1mH	I _{AR}	14		А
Repetitive avalanche energy ^C		E _{AR}	98		mJ
Single pulsed avalanche energy ^G		E _{AS}	555		mJ
MOSFET dv/dt ruggedness		dv/dt	100		V/ns
Diode reverse recovery		dv/dt	20		V/ns
V_{DS} =0 to 400V, I_{F} <=20A, T_{j} =25°C		di/dt	500		A/us
_	T _C =25°C	Pn	312.5	32.5	W
Power Dissipation B	Derate above 25°C	ם י	2.5	0.25	W/°C
Junction and Storage Temperature Range		T_J, T_{STG}	-55 to 150		°C
Maximum lead temperature for soldering purpose, 1/8" from case for 5 seconds		T _L	300		°C

Thermal Characteristics					
Parameter	Symbol	AOW125A60	AOWF125A60	Units	
Maximum Junction-to-Ambient A,D	$R_{\theta JA}$	65	65	°C/W	
Maximum Case-to-sink A	$R_{\theta CS}$	0.5		°C/W	
Maximum Junction-to-Case	$R_{\theta JC}$	0.4	3.8	°C/W	

^{*} Drain current limited by maximum junction temperature.



Electrical Characteristics (T_J=25°C unless otherwise noted)

Symbol	Parameter	Conditions	Min	Тур	Max	Units	
STATIC I	PARAMETERS						
BV _{DSS}	Drain-Source Breakdown Voltage	I _D =250µA, V _{GS} =0V, T _J =25°C	600			\ /	
DV _{DSS}		I _D =250µA, V _{GS} =0V, T _J =150°C		700		- V	
BV _{DSS} /∆TJ	Breakdown Voltage Temperature Coefficient	I _D =250μA, V _{GS} =0V		0.51		V/°C	
I _{DSS} Zero Gate Voltage Drain Curre	Zara Cata Valtaga Drain Current	V _{DS} =600V, V _{GS} =0V			1		
	zero Gate voltage Drain Current	V _{DS} =480V, T _J =125°C			10	μА	
I _{GSS}	Gate-Body leakage current	$V_{DS}=0V, V_{GS}=\pm20V$			±100	nA	
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS}=5V_{,}I_{D}=250\mu A$	3.3	3.9	4.5	V	
R _{DS(ON)}	Static Drain-Source On-Resistance	V _{GS} =10V, I _D =14A		0.108	0.125	Ω	
g _{FS}	Forward Transconductance	V _{DS} =10V, I _D =14A		21		S	
V_{SD}	Diode Forward Voltage	I _S =14A,V _{GS} =0V		0.86	1.2	V	
Is	Maximum Body-Diode Continuous Current				28	Α	
I _{SM}	Maximum Body-Diode Pulsed Current	С			100	Α	
DYNAMI	C PARAMETERS		•	•		•	
C _{iss}	Input Capacitance	V 0V V 100V f 1MH=		2993		pF	
C _{oss}	Output Capacitance	V_{GS} =0V, V_{DS} =100V, f=1MHz		85		pF	
C _{o(er)}	Effective output capacitance, energy related H	V 0V V 0 1- 400V 5 4MU-		73		pF	
C _{o(tr)}	Effective output capacitance, time related	$-V_{GS}$ =0V, V_{DS} =0 to 480V, f=1MHz		305		pF	
C _{rss}	Reverse Transfer Capacitance	V _{GS} =0V, V _{DS} =100V, f=1MHz		0.8		pF	
R _a	Gate resistance	f=1MHz		2.3		Ω	
	ING PARAMETERS		I		ı	I	
Q _q	Total Gate Charge			39		nC	
Q _{qs}	Gate Source Charge	V _{GS} =10V, V _{DS} =480V, I _D =14A		19		nC	
Q _{gd}	Gate Drain Charge	7		9		nC	
t _{D(on)}	Turn-On DelayTime			39		ns	
t _r	Turn-On Rise Time	V _{GS} =10V, V _{DS} =400V, I _D =14A,		34		ns	
t _{D(off)}	Turn-Off DelayTime	$R_G=5\Omega$		56		ns	
t _f	Turn-Off Fall Time			19		ns	
t _{rr}	Body Diode Reverse Recovery Time			375		ns	
I _{rm}	Peak Reverse Recovery Current	I _F =14A, dI/dt=100A/μs, V _{DS} =400V		34		Α	
Q _{rr}	Body Diode Reverse Recovery Charge			8		μС	

A. The value of R $_{\theta JA}$ is measured with the device in a still air environment with T $_A$ =25 $^{\circ}$ C.

APPLICATIONS OR USES AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS ARE NOT AUTHORIZED. AOS DOES NOT ASSUME ANY LIABILITY ARISING OUT OF SUCH APPLICATIONS OR USES OF ITS PRODUCTS. AOS RESERVES THE RIGHT TO MAKE CHANGES TO PRODUCT SPECIFICATIONS WITHOUT NOTICE. IT IS THE RESPONSIBILITY OF THE CUSTOMER TO EVALUATE SUITABILITY OF THE PRODUCT FOR THEIR INTENDED APPLICATION. CUSTOMER SHALL COMPLY WITH APPLICABLE LEGAL REQUIREMENTS, INCLUDING ALL APPLICABLE EXPORT CONTROL RULES, REGULATIONS AND LIMITATIONS.

AOS' products are provided subject to AOS' terms and conditions of sale which are set forth at: http://www.aosmd.com/terms and conditions of sale

B. The power dissipation P_D is based on T_{JIMAX}=150° C, using junction-to-case thermal resistance, and is more useful in setting the upper dissipation limit for cases where additional heatsinking is used.

C. Repetitive rating, pulse width limited by junction temperature $T_{J(MAX)}$ =150° C, Ratings are based on low frequency and duty cycles to keep initial T_J =25° C.

D. The R _{BJA} is the sum of the thermal impedance from junction to case R _{BJC} and case to ambient.

E. The static characteristics in Figures 1 to 6 are obtained using <300µs pulses, duty cycle 0.5% max.


F. These curves are based on the junction-to-case thermal impedance which is measured with the device mounted to a large heatsink, assuming a maximum junction temperature of $T_{J(MAX)}=150^\circ$ C. The SOA curve provides a single pulse rating. G. L=60mH, $I_{AS}=4.3A$, $R_G=25\Omega$, Starting $T_J=25^\circ$ C.


H. $C_{\text{O(er)}}$ is a fixed capacitance that gives the same stored energy as C_{oss} while V_{DS} is rising from 0 to 80% $V_{\text{(BR)DSS}}$.

I. $C_{\text{O(er)}}$ is a fixed capacitance that gives the same charging time as C_{oss} while V_{DS} is rising from 0 to 80% $V_{\text{(BR)DSS}}$.



TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS





0

0

10

 $\label{eq:local_local} I_{D}\left(\mathbf{A}\right)$ Figure 3: On-Resistance vs. Drain Current and Gate Voltage


25

30


35

40


15 20




 $T_J(^{\circ}C)$ Figure 5: Break Down vs. Junction Temparature



V_{GS} (Volts) Figure 2: Transfer Characteristics



Temperature (°C)
Figure 4: On-Resistance vs. Junction Temperature




V_{SD} (Volts) Figure 6: Body-Diode Characteristics

Rev2.1: February 2024 **www.aosmd.com** Page 3 of 6





TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS





TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS







Pulse Width (s)
Figure 14: Normalized Maximum Transient Thermal Impedance for AOWF125A60 (Note F)

Rev2.1: February 2024 www.aosmd.com Page 5 of 6





Gate Charge Test Circuit & Waveform







Resistive Switching Test Circuit & Waveforms







Unclamped Inductive Switching (UIS) Test Circuit & Waveforms





Diode Recovery Test Circuit & Waveforms





Rev2.1: February 2024 **www.aosmd.com** Page 6 of 6