




Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**  
Element Type: **Thin Film**  
Package Size Code: **0805**  
Power Rating: **.1 W**  
Resistance Value: **1.0K  $\Omega$**

Features

Product Type Features

|                   |                    |
|-------------------|--------------------|
| Resistor Type     | Precision Resistor |
| Element Type      | Thin Film          |
| Package Size Code | 0805               |

Configuration Features

|                     |   |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|

Electrical Characteristics

|                             |                           |
|-----------------------------|---------------------------|
| Operating Voltage           | 100 V                     |
| Power Rating                | .1 W                      |
| Resistance Value            | 1.0K $\Omega$             |
| Resistance Class            | 1k $\Omega$ – 1M $\Omega$ |
| Passive Component Tolerance | .1 %                      |

Termination Features

|                                         |        |
|-----------------------------------------|--------|
| Surface Mount Resistor Termination Type | Solder |
| Number of Terminations                  | 2      |



Dimensions

|                |                  |
|----------------|------------------|
| Product Height | .55 mm[.022 in]  |
| Product Length | 2 mm[.079 in]    |
| Product Width  | 1.25 mm[.049 in] |

Usage Conditions

|                             |              |
|-----------------------------|--------------|
| Operating Temperature Range | -55 – 155 °C |
| Temperature Coefficient     | ±25 ppm/°C   |

Industry Standards

|                            |   |
|----------------------------|---|
| Moisture Sensitivity Level | 1 |
|----------------------------|---|

Packaging Features

|                  |                |
|------------------|----------------|
| Packaging Method | Taped & Reeled |
|------------------|----------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JUNE 2024 (241)<br>Does not contain REACH SVHC |
| Halogen Content                               | BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.                                                                          |
| Solder Process Capability                     | Reflow solder capable to 260°C                                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 6-2176238-7

CPF A 0805 100K 0.1% 25PPM 5K RL

Also in the Series | Neohm CPF

Surface Mount Resistors(6123)

Customers Also Bought

TE Part #33460

TERMINAL,SOLIS R 8 10

TE Part #172170-1

12 CIR UNIV M-N-L PLUG

TE Part #34120

TERMINAL,SOLIS R 16-14 6

TE Part #34123

TERMINAL,SOLIS R 16-14 10

TE Part #4-794627-0

10P MICRO MNL ASSY, RA, SMT, L

TE Part #1-794607-1

MICRO MNL RPT CNT STRP 15AU LF

TE Part #T4162123005-004

RPC-M12-5MS-3.0SH-M12-5FS-PUR

TE Part #34112

SOLIS R 22-16COMM 22-18MIL 10





Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_3-2176238-3\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-2176238-3\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-2176238-3\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Automotive Grade Thin Film Chip Resistor - Type CPF-A Series

English