

Passive Components > Resistors > Surface Mount Resistors



Resistor Type: Power Resistor

Element Type: Thin Film

Package Size Code: 1206

Power Rating: 2 W

Resistance Value: 3.48K Ω

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Thin Film
Package Size Code	1206

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	100 V
Power Rating	2 W
Resistance Value	3.48K Ω
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.43 mm [.017 in]
Product Length	3.05 mm [.12 in]
Product Width	1.55 mm [.061 in]

Usage Conditions

Operating Temperature Range	-55 – 155 $^{\circ}$ C
Temperature Coefficient	± 50 ppm/ $^{\circ}$ C

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Reflow solder capable to 260 $^{\circ}$ C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 7-2176524-8
3503G 2B 3K48 1% 1K RL

Also in the Series | CGS 3503



Surface Mount Resistors(534)

Customers Also Bought

TE Part #206043-1
RECEPT,SZ 17-14 CPCTE Part #4-1622820-6
3520 3R9 5%TE Part #640506-3
36P MR HDR ASSY V0TE Part #776164-1
35POS,AMPSEAL,SOC HSG ASSY,SLD,
COD 1TE Part #966140-5
AMP MCP Unsealed HeadersTE Part #174975-2
040 MLC CAP ASSY V 16PTE Part #5178405-1
040 SEALED PAIR MATE 120P CAP
ASSYTE Part #282378-1
070 SERIES TAB CONTACTTE Part #8-1416000-7
V23086C1021A502

Documents

Product Drawings

[3503G 2B 3K48 1% 5K RL](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_7-2176527-8_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-2176527-8_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-2176527-8_A.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Aluminium Nitride Thin Film Power Resistor - Type 3503 Series](#)

English