

5-2371899-2 ✓ ACTIVE


TE Internal #: 5-2371899-2

Board-to-Board, 64 Position, 1 mm [.04 in] Centerline, Vertical, Black, Height 11.25 mm [.44 in], Width 8.2 mm [.32 in], PCI & PCI Express Connectors

[View on TE.com >](#)



Connectors > PCB Connectors > Card Edge Connectors > PCI & PCI Express Connectors



Connector System: **Board-to-Board**

Number of Positions: **64**

PCI Generation: **5**

Centerline (Pitch): **1 mm [.04 in]**

Termination Post & Tail Length: **1.1 mm [.043 in]**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board
Sealable	No

Configuration Features

Number of Positions	64
PCB Mount Orientation	Vertical
Ejector	Without

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Current Rating (Max)	1.1 A
	30 μ in

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Termination Post & Tail Length 1.1 mm [.043 in]

Mechanical Attachment

PCB Mount Retention Type	Metal Hold-Down
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	1 mm [.04 in]
--------------------	---------------

Dimensions

Connector Height	11.25 mm [.44 in]
Connector Width	8.2 mm [.32 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C [-40 – 185 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	High Speed Data
---------------------	-----------------

Industry Standards

PCI Generation	5
----------------	---

Product Compliance

For compliance documentation, visit the product page on TE.com

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products

will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2364427-2
PCIE G5 CON,SMT,64P,15",WO
MYLAR,ST

Customers Also Bought



TE Part #35559
TERMINAL,PIDG SPD 16-14 6



TE Part #5536416-5
ASSY,PIN,EURO,"C",LEAD-FREE,96



TE Part #1-100605-2
250 FASTON,REC.,14-17AWG,PTPB



TE Part #1-2287965-5
6POS, MCON 1.2 LL REC SEALED
2ROW



TE Part #2204888-1
BB1000 ORV3 Output Connector Type
I



TE Part #2389779-3
CA, ITGEAR ORV3 2 FRULE-w/ SENSE
&GRND

Documents

Product Drawings

[PCIE G5 CON,SMT,S-CUT,64P,30",10 MYL,ST](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_5-2371899-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-2371899-2_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-2371899-2_A.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English