




Connectors > Contacts > Connector Contacts



Contact Type: **Socket**

Contact Mating Area Plating Material: **Tin**

Contact Base Material: **Phosphor Bronze**

Product Terminates To: **Printed Circuit Board**

Contact Current Rating (Max): **5 A**

Features

Product Type Features

Applied Pressure	Standard
------------------	----------

Electrical Characteristics

Insulation Resistance	5000 MΩ
Dielectric Withstanding Voltage (Max)	1200 V
Contact Resistance	12 mΩ

Contact Features

PCB Contact Termination Area Plating Material Thickness	2.0066 μm[79 μin]
Contact Mating Area Plating Material Thickness	2.0066 μm[79 μin]
Contact Orientation	Straight
PCB Contact Termination Area Plating Material	Tin
Contact Type	Socket
Contact Mating Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	5 A

Termination Features

Termination Post & Tail Length	2.85 mm[.112 in]
Product Terminates To	Printed Circuit Board

Mechanical Attachment

--	--



Wire Insulation Support	Without
PCB Mount Retention	Without

Housing Features

Mating Entry Location	Top
-----------------------	-----

Dimensions

PCB Thickness (Recommended)	1.4 – 1.78 mm [.055 – .07 in]
-----------------------------	-------------------------------

Usage Conditions

Operating Temperature Range	-65 – 105 °C [-85 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Quantity	5000
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C








Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 86181-2 MOD I KEYING PLUG	 TE Part # 3-5086147-7 MOD I POST PLTD SN, ROHS	 TE Part # 6-87160-1 10 MOD I HDR SRST .156CL, ROHS	 TE Part # 1-5086147-0 MOD I POST PLTD SN, ROHS
 TE Part # 2-5086147-2 MOD I POST PLTD SN, ROHS	 TE Part # 2-5086182-2 MOD I POST LP, ROHS	 TE Part # 5-87655-2 02 MOD I HDR SRRA .156CL, ROHS	 TE Part # 5086147-1 MOD I POST PLTD SN, ROHS
 TE Part # 5086147-2 MOD I POST PLTD SN, ROHS	 TE Part # 5086147-9 MOD I POST PLTD SN, ROHS	 TE Part # 5-85875-3 09 MOD I HDR SRST .156CL, ROHS	 TE Part # 5-87160-4 02 MOD I HDR SRST .156CL, ROHS
 TE Part # 5-87194-4 05 MOD I HDR SRRA .156CL, ROHS	 TE Part # 7-85875-0 19 MOD I HDR SRST .156CL, ROHS	 TE Part # 7-87160-0 20 MOD I HDR SRST .156CL, ROHS	TE Part # 87003-3 MOD I RECP STMPD

Also in the Series | AMPMODU MOD 1



Automotive Terminals(4)



Board-to-Board Jumpers & Shunts(5)




Connector Contacts(106)



Connector Hardware(2)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(341)




Wire-to-Board Connector Assemblies & Housings(20)

Customers Also Bought



TE Part #213782-4
CPC RECPT ASSEMBLY SIZE 23-19



TE Part #1623793-6
SQP5 240R 5% MTL FLM



TE Part #1-1241152-0
10P HV100 REC. CON, SMD, GOLD, BLISTER




TE Part #1-969973-0
2x10P HV100 REC. CON, SMD, GOLD, BLISTER




TE Part #829131P021
ES2000-NO.1-C1-0-STK




TE Part #969973-7
2x7P HV100 REC. CON, SMD, GOLD, BLISTER



TE Part #5-2176349-0
CRGCQ 2512 120K 1%



TE Part #1-2176330-2
CRGP 2010 82R 1%



TE Part #86182-7
MOD I POST LP

Documents



Product Drawings

MOD I RECP STMPD

English

Product Specifications

Application Specification

English