




Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers >

Heavy Duty Sealed Connector Series Cap



Protection & Strain Relief Accessory Type: **Cover**

Cable Exit Angle: **180°**

Strain Relief: **Without**

Primary Product Color: **Black**

Primary Product Material: **PBT GF**

[All Heavy Duty Sealed Connector Series Cap \(10\)](#)

Features

Product Type Features

|                                           |       |
|-------------------------------------------|-------|
| Protection & Strain Relief Accessory Type | Cover |
|-------------------------------------------|-------|

Configuration Features

|                     |      |
|---------------------|------|
| Number of Positions | 2, 3 |
|---------------------|------|

Body Features

|                          |        |
|--------------------------|--------|
| Cable Exit Angle         | 180°   |
| Primary Product Color    | Black  |
| Primary Product Material | PBT GF |

Mechanical Attachment

|               |         |
|---------------|---------|
| Strain Relief | Without |
|---------------|---------|

Usage Conditions

|                                 |                              |
|---------------------------------|------------------------------|
| Compatible With Connector Style | Housing For Female Terminals |
|---------------------------------|------------------------------|



|                             |                                                                                                                                                                                           |
|-----------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Operating Temperature (Max) | 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F] |
| Operating Temperature Range | -40 – 140 °C[-40 – 284 °F]                                                                                                                                                                |

Industry Standards

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|

Packaging Features

|                    |      |
|--------------------|------|
| Packaging Quantity | 1000 |
| Packaging Method   | Box  |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JUNE 2024 (241)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                  |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                    |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-H3399-CH8172  
Heavy Duty Sealed Connector Series Housings

Also in the Series

Heavy Duty Sealed Connector Series

Automotive Connector Caps & Covers (25)

Automotive Housings(207)

Connector Seals & Cavity Plugs(5)

Data Connectivity Headers(2)

Data Connectivity Housings(16)

Other Automotive Connector Accessories(34)

PCB Headers & Receptacles(1)

Customers Also Bought

TE Part #1718328-1  
LEAVYSEAL Locking Slides

TE Part #DTMH04-2PA  
REC, 2P, BLK, N, HI TEMP, A

TE Part #2278730-1  
3P CAN CONNECTOR, RECEPTACLE


TE Part #DT04-2P-C017  
REC, 2P, GRY, BLOCKED

TE Part #1823444-1  
ADAPTER, FOR A-PILLAR, ASSY

TE Part #2203698-1  
2P MCON UNSEALED PLUG WIRE DRESS

TE Part #2278730-2  
3P CAN CONNECTOR, RECEPTACLE

TE Part #87805-000  
PSS-X1379B WITH BRACKET



Documents

Product Drawings

PROTECTION CAP, FOR REC.HSG GR

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2112299-1\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2112299-1\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2112299-1\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

HDSCS CAN Bus Y-Connector and 120 Resistor Brochure

English

HDSCS Catalog

English

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English