



Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Protective Cover**

Strain Relief: **Without**

Primary Product Color: **Gray**

Primary Product Material: **PVC**

Number of Positions: **12**

Features

Product Type Features

Sealable	No
Protection & Strain Relief Accessory Type	Protective Cover

Configuration Features

Number of Positions	12
---------------------	----

Body Features

Primary Product Color	Gray
Primary Product Material	PVC

Mechanical Attachment

Strain Relief	Without
---------------	---------

Usage Conditions

Compatible With Connector Style	Receptacle
Operating Temperature (Max)	100 °C[212 °F]
Operating Temperature Range	-29 – 100 °C[-20 – 212 °F]

Industry Standards

Degree of Protection	Not Tested
----------------------	------------

Packaging Features

Packaging Method	Box
------------------	-----



Other

Serviceable	Yes
-------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-D485-CH8172
DEUTSCH DTM Housings



TE Part # DTM04-12PA-EE04
REC, 12P, BLK, N, HIGH TEMP, A



TE Part # 1-2303064-1
12POS,STAMPED 20,PIN HSG ASSY, SLD,COD 1



TE Part # DTM04-12PC-L012
REC, 12P, GRN, N, FLANGE, C

DTM12P-DC

Protective Cover, Gray, PVC, 12 Position, -29 – 100 °C [-20 – 212 °F], DEUTSCH DTM,
Automotive Connector Caps & Covers



TE Part # DTM04-12PD-L012
REC, 12P, BRN, N, FLANGE, D

TE Part # 2303064-2
REC, 12P, BLK, N, FLANGE, B

TE Part # DTM04-12PC-EE04
REC, 12P, BLK, N, HIGH TEMP, C

Also in the Series | DEUTSCH DT

Automotive Connector Caps & Covers
(19)

Automotive Connector Locks &
Position Assurance(87)

Automotive Housings(706)

Connector Backshells(61)

Connector Seals & Cavity Plugs(6)

Connector Strain Relief(28)

Insertion & Extraction Tools(3)


Other Automotive Connector
Accessories(28)

PCB Headers & Receptacles(106)

Also in the Series | DEUTSCH DTM



Automotive Connector Caps & Covers (7)



Automotive Connector Locks & Position Assurance(25)



Automotive Housings(104)




Connector Backshells(7)



Connector Strain Relief(28)



Insertion & Extraction Tools(2)



PCB Headers & Receptacles(38)

Customers Also Bought



TE Part #776536-2
AS16,CAP ASSY,ST,04P,E SEAL,CODE B



TE Part #2-1703773-1
6POS,TAB 1.6X0.6,PIN HSG,ASSY



TE Part #2-2112162-1
21POS,TAB2.8X0.8,TABHSG,CODE B, ASSY,SLD



TE Part #DT06-2S-LC01
PLG, 2P, BLK, E, SL RT, DIN BKSHL ADPT



TE Part #4828-007-8605
BKSHL, 86P, BLK, VERTICAL, DRCP



TE Part #2329383-2
PB OFF/ON FC RED M1 TERM. IP68



TE Part #DT04-12PA-LE06
REC, 12P, GRY, E, CAP, FLANGE, A



TE Part #DRC23-40PB-N012
HDR, 40P, BLK, RA, AU/NI/CU, B



TE Part #2325098-2
MNTG CLIP,ENETSEAL PLUS



TE Part #2325106-1
ADAPTER,2POS,1.2X0.6,PIN HSG ASSY

Documents



Product Drawings

PROTECT CVR, 12P, REC, GRY, DTM

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_DTM12P-DC_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_DTM12P-DC_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_DTM12P-DC_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English