

Part Number : 936030097

Product Description : GWconnect STD - Standard, Single Lever Bulkhead Mount Housing, Polyamide, with 1 Lever, Side Entry, with Cable Gland, Size «32x13», Pg21 Thread, Black

Series Number : 93601

Status : Active

Product Category : Heavy-Duty Connectors

Engineering Number : 7908.6664.1



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	Heavy-Duty Connectors
Series	93601
Description	GWconnect STD - Standard, Single Lever Bulkhead Mount Housing, Polyamide, with 1 Lever, Side Entry, with Cable Gland, Size «32x13», Pg21 Thread, Black
Component Type	Single Lever Bulkhead Housing
IP Rating	IP66, IP67
Product Family	GWconnect Heavy Duty Connectors (HDC)
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191842677

Agency

CSA	256883
UL	E249674

Electrical

Voltage - Maximum	500V
-------------------	------

Physical

Cable Diameter	11.00-18.00mm
Component Size	«32X13»
Entry Location	Side
Flammability	UL 94V-0
Gland Color	Black RAL 9005
Housing Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Cable Gland	Polyamide
Material - Housing	Polyamide
Material - Lever	Polyamide
Mounting Style	Bulkhead
Net Weight	46.000/g

Number of Levers	1
Packaging Type	Bag
Thread Size	Pg21
Thread Type	(Pg)

Use with Part(s)

Description	Part Number
Use With	Size «32x13» S-QD Inserts

Kit Component Parts

This document was generated on Oct 14, 2024