



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Current Sensing Resistor**

Element Type: **Thick Film**

Package Size Code: **2512**

Power Rating: **2 W**

Resistance Value: **.453 Ω**

Features

Product Type Features

|                   |                          |
|-------------------|--------------------------|
| Resistor Type     | Current Sensing Resistor |
| Element Type      | Thick Film               |
| Package Size Code | 2512                     |

Configuration Features

|                     |   |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|

Electrical Characteristics

|                             |           |
|-----------------------------|-----------|
| Power Rating                | 2 W       |
| Resistance Value            | .453 Ω    |
| Resistance Class            | Up to 1kΩ |
| Passive Component Tolerance | 1 %       |

Termination Features

|                                         |        |
|-----------------------------------------|--------|
| Surface Mount Resistor Termination Type | Solder |
| Number of Terminations                  | 2      |

Dimensions





|                |                 |
|----------------|-----------------|
| Product Height | .74 mm[.029 in] |
| Product Length | 6.35 mm[.25 in] |
| Product Width  | 3.1 mm[.122 in] |

Usage Conditions

|                             |              |
|-----------------------------|--------------|
| Operating Temperature Range | -55 – 155 °C |
| Temperature Coefficient     | ±50 ppm/°C   |

Packaging Features

|                  |                |
|------------------|----------------|
| Packaging Method | Taped & Reeled |
|------------------|----------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JUNE 2024 (241)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                             |
| Solder Process Capability                     | Reflow solder capable to 260°C                                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

RLC73PD3AR453FTDG

Current Sensing Resistor, Thick Film, 2512, 2 W, .453 ohm, 1 %, ±50 ppm/°C, Solder, 2 Termination, Height .74 mm [.029 in], CGS RLC73



TE Part # 8-2176607-8

[RLC73PD 3A R453 1% 1K RL](#)

Also in the Series | [CGS RLC73](#)

[Surface Mount Resistors\(2392\)](#)

Customers Also Bought

TE Part #4-2176601-8

[RLC73K 3A R174 1% 4K RL](#)

TE Part #2176602-4

[RLC73K 3A R649 1% 4K RL](#)

TE Part #1-2176602-5

[RLC73K 3A R845 1% 4K RL](#)

TE Part #1-2176602-8

[RLC73K 3A R909 1% 4K RL](#)

TE Part #5053142385

[RNF-100-3/8-BK-STK](#)

Documents

[Product Drawings](#)  
[RLC73PD 3A R453 1% 2K RL](#)

English

[CAD Files](#)  
Customer View Model  
[ENG\\_CVM\\_CVM\\_8-2176605-8\\_BA.3d\\_igs.zip](#)



English

Customer View Model

[ENG\\_CVM\\_CVM\\_8-2176605-8\\_BA.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_8-2176605-8\\_BA.2d\\_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SMD Low Ohmic - Current Sense Resistors - Type RLC73 Series](#)

English