




P-Channel 40-V (D-S) 175 °C MOSFET

PRODUCT SUMMARY

V_{DS} (V)	$r_{DS(on)}$ (Ω)	I_D (A)
- 40	0.013 at $V_{GS} = - 10$ V	- 60 ^a
	0.022 at $V_{GS} = - 4.5$ V	- 48


FEATURES

- TrenchFET[®] Power MOSFET
- 175 °C Junction Temperature

RoHS
COMPLIANT

Drain Connected to Tab

Ordering Information: SUD50P04-13L-E3 (Lead (Pb)-free)



P-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS $T_A = 25$ °C, unless otherwise noted

Parameter	Symbol	Limit	Unit
Drain-Source Voltage	V_{DS}	- 40	V
Gate-Source Voltage	V_{GS}	± 20	
Continuous Drain Current ^b	$T_C = 25$ °C	I_D	- 60 ^c
	$T_C = 100$ °C		- 43
Pulsed Drain Current	I_{DM}	- 100	
Continuous Source Current (Diode Conduction)	I_S	- 60 ^c	
Avalanche Current	I_{AS}	- 40	
Avalanche Energy,	$L = 0.1$ mH E_{AS}	80	mJ
Maximum Power Dissipation ^b	$T_C = 25$ °C	P_D	93.7 ^b
	$T_A = 25$ °C		3 ^a
Operating Junction and Storage Temperature Range	T_J, T_{stg}	- 55 to 175	°C

THERMAL RESISTANCE RATINGS

Parameter	Symbol	Typical	Maximum	Unit
Maximum Junction-to-Ambient ^a	$t \leq 10$ sec	R_{thJA}	15	°C/W
	Steady State		40	
Maximum Junction-to-Case (Drain)	R_{thJC}	1.3	1.8	

Notes:

a. Surface Mounted on 1" x 1" FR4 board.

b. See SOA curve for voltage derating.







b. Calculated based on maximum allowed Junction Temperature. Package limitation current is 50 A.

SPECIFICATIONS $T_J = 25\text{ }^{\circ}\text{C}$, unless otherwise noted						
Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Static						
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS} = 0\text{ V}$, $I_D = - 250\text{ }\mu\text{A}$	- 40			V
Gate-Source Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}$, $I_D = - 250\text{ }\mu\text{A}$	- 1.0		- 3.0	
Gate-Source Leakage	I_{GSS}	$V_{DS} = 0\text{ V}$, $V_{GS} = \pm 20\text{ V}$			± 100	nA
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = - 40\text{ V}$, $V_{GS} = 0\text{ V}$			- 1	μA
		$V_{DS} = - 40\text{ V}$, $V_{GS} = 0\text{ V}$, $T_J = 125\text{ }^{\circ}\text{C}$			- 50	
On-State Drain Current ^a	$I_{D(on)}$	$V_{DS} = - 5\text{ V}$, $V_{GS} = - 10\text{ V}$	- 50			A
Drain-Source On-State Resistance ^a	$r_{DS(on)}$	$V_{GS} = - 10\text{ V}$, $I_D = - 30\text{ A}$		0.0105	0.013	Ω
		$V_{GS} = - 10\text{ V}$, $I_D = - 30\text{ A}$, $T_J = 125\text{ }^{\circ}\text{C}$			0.020	
		$V_{GS} = - 4.5\text{ V}$, $I_D = - 20\text{ A}$		0.017	0.022	
Forward Transconductance ^a	g_{fs}	$V_{DS} = - 15\text{ V}$, $I_D = - 30\text{ A}$	15			S
Dynamic ^b						
Input Capacitance	C_{iss}	$V_{DS} = - 25\text{ V}$, $V_{GS} = 0\text{ V}$, $f = 1\text{ MHz}$		3120		pF
Output Capacitance	C_{oss}			440		
Reverse Transfer Capacitance	C_{rss}			320		
Gate Resistance	R_g	$f = 1\text{ MHz}$		4.3		Ω
Total Gate Charge ^c	Q_g	$V_{DS} = - 20\text{ V}$, $V_{GS} = - 10\text{ V}$, $I_D = - 50\text{ A}$		63	95	nC
Gate-Source Charge ^c	Q_{gs}			13		
Gate-Drain Charge ^c	Q_{gd}			16		
Turn-On Delay Time ^c	$t_{d(on)}$	$V_{DD} = - 20\text{ V}$, $R_L = 0.4\text{ }\Omega$ $I_D \cong - 50\text{ A}$, $V_{GEN} = - 10\text{ V}$, $R_g = 2.5\text{ }\Omega$		15	25	ns
Rise Time ^c	t_r			18	30	
Turn-Off Delay Time ^c	$t_{d(off)}$			60	90	
Fall Time ^c	t_f			47	70	
Drain-Source Body Diode Characteristics						
Pulse Current	I_{SM}				- 100	
Forward Voltage ^a	V_{SD}	$I_F = - 50\text{ A}$, $V_{GS} = 0\text{ V}$		- 1.0	- 1.5	V
Source-Drain Reverse Recovery Time	t_{rr}	$I_F = - 50\text{ A}$, $di/dT = 100\text{ A}/\mu\text{s}$		36	55	ns

Notes:






- a. Pulse test; pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$.
b. Guaranteed by design, not subject to production testing.
c. Independent of operating temperature.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

**TYPICAL CHARACTERISTICS** 25 °C unless noted**Output Characteristics****Transfer Characteristics****Transconductance****On-Resistance vs. Drain Current****Capacitance****Gate Charge**


SUD50P04-13L

Vishay Siliconix

**TYPICAL CHARACTERISTICS** 25 °C unless noted**THERMAL RATINGS**



THERMAL RATINGS



Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see <http://www.vishay.com/ppg?73009>



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.