


FMN CONNECTOR



1.0 mm pitch/Connectors for PC board/For FFC • Non-ZIF Type



This connector is 1.0 mm pitch for FFC connection. Realized low cost multi-core by adopting contact structure on one side. In addition, it is a multi-entry type connector that has both DIP and SMT types.

- Compact, High-density design
- Contact structure on one side
- Heat resistant design suitable for surface mounting
- Applicable to automatic mounting by embossed-taping

Specifications

- Current rating: 0.5 A DC
- Voltage rating: 50 V DC
- Temperature range: -25°C to +85°C
(including temperature rise in applying electrical current)
- Contact resistance: Initial value/ 30 mΩ max.
After environmental tests/ 50 mΩ max.
- Insulation resistance: 500 MΩ min.
- Withstanding voltage: 500 VAC/minute
- Applicable FFC: Conductor pitch/ 1.0 mm
Conductor width/ 0.7 mm
Mating part thickness/ 0.3 ± 0.05 mm
- Applicable PC board thickness: 1.6 mm
Note: FFC to be actually used should be checked for applicability.
- * In using the products, refer to "Handling Precautions for Terminals and Connectors" described on our website (Technical documents of Product information page).
- * RoHS2 compliance
- * Dimensional unit: mm
- * Contact JST for details.

Standards

- ☑ Recognized E60389
- ☑ Certified LR20812


FMN CONNECTOR

PC board layout and Assembly layout



<DIP type>

Top entry type

•Normal type




•Reverse type





Side entry type

•Normal type



•Reverse type





<SMT type>



Top entry type

<In-line>

•Normal type





•Reverse type





<Staggered>



•Normal type



•Reverse type



Side entry type




Note:

1. The above figure is the figure viewed from the connector mounting side.
2. Tolerances are non-cumulative: ± 0.05 mm for all centers.
3. Hole dimensions differ according to the type of PC board and piercing method.
The dimensions above should serve as a guideline. Contact JST for details.

FMN CONNECTOR


Lead section dimensions of FFC



Note: N --- Number of circuits


DIP type Connector

Top entry type




<Note> Normal type: The solder tail for circuit No.1 contact is positioned in front.
Reverse type: The solder tail for circuit No.1 contact is positioned behind.

Side entry type



Side entry type with stop



No. of circuits	Model No.						Dimensions (mm)			Q'ty/box		
	Top entry type		Side entry type		Side entry type with stop		A	B	C	Top entry type	Side entry type	Side entry type with stop
	Normal type	Reverse type	Normal type	Reverse type	Normal type	Reverse type						
4	04FMN-BTK-A	04FMN-BTRK-A	04FMN-STK-A	04FMN-STRK-A	04FMN-SSTK-A	04FMN-SSTRK-A	3.0	6.0	5.0	3,600	2,160	2,520
5	05FMN-BTK-A	05FMN-BTRK-A	05FMN-STK-A	05FMN-STRK-A	05FMN-SSTK-A	05FMN-SSTRK-A	4.0	7.0	6.0	3,100	1,860	2,170
6	06FMN-BTK-A	06FMN-BTRK-A	06FMN-STK-A	06FMN-STRK-A	06FMN-SSTK-A	06FMN-SSTRK-A	5.0	8.0	7.0	2,700	1,620	1,890
7	07FMN-BTK-A	07FMN-BTRK-A	07FMN-STK-A	07FMN-STRK-A	07FMN-SSTK-A	07FMN-SSTRK-A	6.0	9.0	8.0	2,400	1,440	1,680
8	08FMN-BTK-A	08FMN-BTRK-A	08FMN-STK-A	08FMN-STRK-A	08FMN-SSTK-A	08FMN-SSTRK-A	7.0	10.0	9.0	2,100	1,260	1,470
9	09FMN-BTK-A	09FMN-BTRK-A	09FMN-STK-A	09FMN-STRK-A	09FMN-SSTK-A	09FMN-SSTRK-A	8.0	11.0	10.0	1,900	1,140	1,330
10	10FMN-BTK-A	10FMN-BTRK-A	10FMN-STK-A	10FMN-STRK-A	10FMN-SSTK-A	10FMN-SSTRK-A	9.0	12.0	11.0	1,800	1,080	1,260
11	11FMN-BTK-A	11FMN-BTRK-A	11FMN-STK-A	11FMN-STRK-A	11FMN-SSTK-A	11FMN-SSTRK-A	10.0	13.0	12.0	1,600	960	1,120
12	12FMN-BTK-A	12FMN-BTRK-A	12FMN-STK-A	12FMN-STRK-A	12FMN-SSTK-A	12FMN-SSTRK-A	11.0	14.0	13.0	1,500	900	1,050
13	13FMN-BTK-A	13FMN-BTRK-A	13FMN-STK-A	13FMN-STRK-A	13FMN-SSTK-A	13FMN-SSTRK-A	12.0	15.0	14.0	1,400	840	980
14	14FMN-BTK-A	14FMN-BTRK-A	14FMN-STK-A	14FMN-STRK-A	14FMN-SSTK-A	14FMN-SSTRK-A	13.0	16.0	15.0	1,300	780	910
15	15FMN-BTK-A	15FMN-BTRK-A	15FMN-STK-A	15FMN-STRK-A	15FMN-SSTK-A	15FMN-SSTRK-A	14.0	17.0	16.0	1,200	720	840
16	16FMN-BTK-A	16FMN-BTRK-A	16FMN-STK-A	16FMN-STRK-A	16FMN-SSTK-A	16FMN-SSTRK-A	15.0	18.0	17.0	1,200	720	840
17	17FMN-BTK-A	17FMN-BTRK-A	17FMN-STK-A	17FMN-STRK-A	17FMN-SSTK-A	17FMN-SSTRK-A	16.0	19.0	18.0	1,100	660	770
18	18FMN-BTK-A	18FMN-BTRK-A	18FMN-STK-A	18FMN-STRK-A	18FMN-SSTK-A	18FMN-SSTRK-A	17.0	20.0	19.0	1,000	600	700
19	19FMN-BTK-A	19FMN-BTRK-A	19FMN-STK-A	19FMN-STRK-A	19FMN-SSTK-A	19FMN-SSTRK-A	18.0	21.0	20.0	1,000	600	700
20	20FMN-BTK-A	20FMN-BTRK-A	20FMN-STK-A	20FMN-STRK-A	20FMN-SSTK-A	20FMN-SSTRK-A	19.0	22.0	21.0	900	540	630
21	21FMN-BTK-A	21FMN-BTRK-A	21FMN-STK-A	21FMN-STRK-A	21FMN-SSTK-A	21FMN-SSTRK-A	20.0	23.0	22.0	900	540	630
22	22FMN-BTK-A	22FMN-BTRK-A	22FMN-STK-A	22FMN-STRK-A	22FMN-SSTK-A	22FMN-SSTRK-A	21.0	24.0	23.0	900	540	630
23	23FMN-BTK-A	23FMN-BTRK-A	23FMN-STK-A	23FMN-STRK-A	23FMN-SSTK-A	23FMN-SSTRK-A	22.0	25.0	24.0	800	480	560
24	24FMN-BTK-A	24FMN-BTRK-A	24FMN-STK-A	24FMN-STRK-A	24FMN-SSTK-A	24FMN-SSTRK-A	23.0	26.0	25.0	800	480	560
25	25FMN-BTK-A	25FMN-BTRK-A	25FMN-STK-A	25FMN-STRK-A	25FMN-SSTK-A	25FMN-SSTRK-A	24.0	27.0	26.0	800	480	560
26	26FMN-BTK-A	26FMN-BTRK-A	26FMN-STK-A	26FMN-STRK-A	26FMN-SSTK-A	26FMN-SSTRK-A	25.0	28.0	27.0	700	420	490
27	27FMN-BTK-A	27FMN-BTRK-A	27FMN-STK-A	27FMN-STRK-A	27FMN-SSTK-A	27FMN-SSTRK-A	26.0	29.0	28.0	700	420	490
28	28FMN-BTK-A	28FMN-BTRK-A	28FMN-STK-A	28FMN-STRK-A	28FMN-SSTK-A	28FMN-SSTRK-A	27.0	30.0	29.0	700	420	490
29	29FMN-BTK-A	29FMN-BTRK-A	29FMN-STK-A	29FMN-STRK-A	29FMN-SSTK-A	29FMN-SSTRK-A	28.0	31.0	30.0	700	420	490
30	30FMN-BTK-A	30FMN-BTRK-A	30FMN-STK-A	30FMN-STRK-A	30FMN-SSTK-A	30FMN-SSTRK-A	29.0	32.0	31.0	600	360	420
31	31FMN-BTK-A	31FMN-BTRK-A	31FMN-STK-A	31FMN-STRK-A	31FMN-SSTK-A	31FMN-SSTRK-A	30.0	33.0	32.0	600	360	420
32	32FMN-BTK-A	32FMN-BTRK-A	32FMN-STK-A	32FMN-STRK-A	32FMN-SSTK-A	32FMN-SSTRK-A	31.0	34.0	33.0	600	360	420
33	33FMN-BTK-A	33FMN-BTRK-A	33FMN-STK-A	33FMN-STRK-A	33FMN-SSTK-A	33FMN-SSTRK-A	32.0	35.0	34.0	600	360	420
34	34FMN-BTK-A	34FMN-BTRK-A	34FMN-STK-A	34FMN-STRK-A	34FMN-SSTK-A	34FMN-SSTRK-A	33.0	36.0	35.0	600	360	420
35	35FMN-BTK-A	35FMN-BTRK-A	35FMN-STK-A	35FMN-STRK-A	35FMN-SSTK-A	35FMN-SSTRK-A	34.0	37.0	36.0	500	300	350
36	36FMN-BTK-A	36FMN-BTRK-A	36FMN-STK-A	36FMN-STRK-A	36FMN-SSTK-A	36FMN-SSTRK-A	35.0	38.0	37.0	500	300	350
37	37FMN-BTK-A	37FMN-BTRK-A	37FMN-STK-A	37FMN-STRK-A	37FMN-SSTK-A	37FMN-SSTRK-A	36.0	39.0	38.0	500	300	350
38	38FMN-BTK-A	38FMN-BTRK-A	38FMN-STK-A	38FMN-STRK-A	38FMN-SSTK-A	38FMN-SSTRK-A	37.0	40.0	39.0	500	300	350
39	39FMN-BTK-A	39FMN-BTRK-A	39FMN-STK-A	39FMN-STRK-A	39FMN-SSTK-A	39FMN-SSTRK-A	38.0	41.0	40.0	500	300	350
40	40FMN-BTK-A	40FMN-BTRK-A	40FMN-STK-A	40FMN-STRK-A	40FMN-SSTK-A	40FMN-SSTRK-A	39.0	42.0	41.0	500	300	350

Material and Finish

Contact: Phosphor bronze, copper-undercoated, tin-plated (reflow treatment)
Housing: 4 to 22 circuits/PBT, UL94V-0, Normal type--gray Reverse type--brown
23 to 40 circuits/PA 6T, UL94V-0, Normal type--gray Reverse type--black

RoHS2 compliance This product displays (LF)(SN) on a label.


FMN CONNECTOR

SMT type Connector


Top entry type

<In-line>

●Normal type




●Reverse type




<Staggered>


●Normal type



●Reverse type



Side entry type



No. of circuits	Model No.					Dimensions (mm)				Q'ty/reel	
	Top entry type				Side entry type	A					
	In-line		Staggered			B			C		
	Normal type	Reverse type	Normal type	Reverse type		Top entry type	Side entry type	Top entry type		Side entry type	
4	04FMN-BMT-A-TF	04FMN-BMTR-A-TB	04FMN-BMTTN-A-TF	04FMN-BMTTR-A-TB	04FMN-SMT-A-TF	3.0	6.0	7.0	5.0	1,000	2,000
5	05FMN-BMT-A-TF	05FMN-BMTR-A-TB	05FMN-BMTTN-A-TF	05FMN-BMTTR-A-TB	05FMN-SMT-A-TF	4.0	7.0	8.0	6.0	1,000	2,000
6	06FMN-BMT-A-TF	06FMN-BMTR-A-TB	06FMN-BMTTN-A-TF	06FMN-BMTTR-A-TB	06FMN-SMT-A-TF	5.0	8.0	9.0	7.0	1,000	2,000
7	07FMN-BMT-A-TF	07FMN-BMTR-A-TB	07FMN-BMTTN-A-TF	07FMN-BMTTR-A-TB	07FMN-SMT-A-TF	6.0	9.0	10.0	8.0	1,000	2,000
8	08FMN-BMT-A-TF	08FMN-BMTR-A-TB	08FMN-BMTTN-A-TF	08FMN-BMTTR-A-TB	08FMN-SMT-A-TF	7.0	10.0	11.0	9.0	1,000	2,000
9	09FMN-BMT-A-TF	09FMN-BMTR-A-TB	09FMN-BMTTN-A-TF	09FMN-BMTTR-A-TB	09FMN-SMT-A-TF	8.0	11.0	12.0	10.0	1,000	2,000
10	10FMN-BMT-A-TF	10FMN-BMTR-A-TB	10FMN-BMTTN-A-TF	10FMN-BMTTR-A-TB	10FMN-SMT-A-TF	9.0	12.0	13.0	11.0	1,000	2,000
11	11FMN-BMT-A-TF	11FMN-BMTR-A-TB	11FMN-BMTTN-A-TF	11FMN-BMTTR-A-TB	11FMN-SMT-A-TF	10.0	13.0	14.0	12.0	1,000	2,000
12	12FMN-BMT-A-TF	12FMN-BMTR-A-TB	12FMN-BMTTN-A-TF	12FMN-BMTTR-A-TB	12FMN-SMT-A-TF	11.0	14.0	15.0	13.0	1,000	2,000
13	13FMN-BMT-A-TF	13FMN-BMTR-A-TB	13FMN-BMTTN-A-TF	13FMN-BMTTR-A-TB	13FMN-SMT-A-TF	12.0	15.0	16.0	14.0	1,000	2,000
14	14FMN-BMT-A-TF	14FMN-BMTR-A-TB	14FMN-BMTTN-A-TF	14FMN-BMTTR-A-TB	14FMN-SMT-A-TF	13.0	16.0	17.0	15.0	1,000	2,000
15	15FMN-BMT-A-TF	15FMN-BMTR-A-TB	15FMN-BMTTN-A-TF	15FMN-BMTTR-A-TB	15FMN-SMT-A-TF	14.0	17.0	18.0	16.0	1,000	2,000
16	16FMN-BMT-A-TF	16FMN-BMTR-A-TB	16FMN-BMTTN-A-TF	16FMN-BMTTR-A-TB	16FMN-SMT-A-TF	15.0	18.0	19.0	17.0	1,000	2,000
17	17FMN-BMT-A-TF	17FMN-BMTR-A-TB	17FMN-BMTTN-A-TF	17FMN-BMTTR-A-TB	17FMN-SMT-A-TF	16.0	19.0	20.0	18.0	1,000	2,000
18	18FMN-BMT-A-TF	18FMN-BMTR-A-TB	18FMN-BMTTN-A-TF	18FMN-BMTTR-A-TB	18FMN-SMT-A-TF	17.0	20.0	21.0	19.0	1,000	2,000
19	19FMN-BMT-A-TF	19FMN-BMTR-A-TB	19FMN-BMTTN-A-TF	19FMN-BMTTR-A-TB	19FMN-SMT-A-TF	18.0	21.0	22.0	20.0	1,000	2,000
20	20FMN-BMT-A-TF	20FMN-BMTR-A-TB	20FMN-BMTTN-A-TF	20FMN-BMTTR-A-TB	20FMN-SMT-A-TF	19.0	22.0	23.0	21.0	1,000	2,000
21	21FMN-BMT-A-TF	21FMN-BMTR-A-TB	—	21FMN-BMTTR-A-TB	21FMN-SMT-A-TF	20.0	23.0	24.0	22.0	1,000	2,000
22	22FMN-BMT-A-TF	22FMN-BMTR-A-TB	22FMN-BMTTN-A-TF	22FMN-BMTTR-A-TB	22FMN-SMT-A-TF	21.0	24.0	25.0	23.0	1,000	2,000
23	23FMN-BMT-A-TF	23FMN-BMTR-A-TB	23FMN-BMTTN-A-TF	23FMN-BMTTR-A-TB	23FMN-SMT-A-TF	22.0	25.0	26.0	24.0	1,000	2,000
24	24FMN-BMT-A-TF	24FMN-BMTR-A-TB	24FMN-BMTTN-A-TF	24FMN-BMTTR-A-TB	24FMN-SMT-A-TF	23.0	26.0	27.0	25.0	1,000	2,000
25	25FMN-BMT-A-TF	25FMN-BMTR-A-TB	25FMN-BMTTN-A-TF	25FMN-BMTTR-A-TB	25FMN-SMT-A-TF	24.0	27.0	28.0	26.0	1,000	2,000
26	26FMN-BMT-A-TF	26FMN-BMTR-A-TB	26FMN-BMTTN-A-TF	—	26FMN-SMT-A-TF	25.0	28.0	29.0	27.0	1,000	2,000
27	27FMN-BMT-A-TF	27FMN-BMTR-A-TB	27FMN-BMTTN-A-TF	27FMN-BMTTR-A-TB	27FMN-SMT-A-TF	26.0	29.0	30.0	28.0	1,000	2,000
28	—	28FMN-BMTR-A-TB	28FMN-BMTTN-A-TF	28FMN-BMTTR-A-TB	28FMN-SMT-A-TF	27.0	30.0	31.0	29.0	1,000	2,000
29	29FMN-BMT-A-TF	29FMN-BMTR-A-TB	29FMN-BMTTN-A-TF	29FMN-BMTTR-A-TB	29FMN-SMT-A-TF	28.0	31.0	32.0	30.0	1,000	2,000
30	30FMN-BMT-A-TF	30FMN-BMTR-A-TB	30FMN-BMTTN-A-TF	30FMN-BMTTR-A-TB	30FMN-SMT-A-TF	29.0	32.0	33.0	31.0	1,000	2,000
31	31FMN-BMT-A-TF	31FMN-BMTR-A-TB	31FMN-BMTTN-A-TF	31FMN-BMTTR-A-TB	31FMN-SMT-A-TF	30.0	33.0	34.0	32.0	1,000	2,000
32	32FMN-BMT-A-TF	32FMN-BMTR-A-TB	32FMN-BMTTN-A-TF	32FMN-BMTTR-A-TB	32FMN-SMT-A-TF	31.0	34.0	35.0	33.0	1,000	2,000
33	33FMN-BMT-A-TF	—	33FMN-BMTTN-A-TF	33FMN-BMTTR-A-TB	33FMN-SMT-A-TF	32.0	35.0	36.0	34.0	1,000	2,000
34	34FMN-BMT-A-TF	—	34FMN-BMTTN-A-TF	34FMN-BMTTR-A-TB	34FMN-SMT-A-TF	33.0	36.0	37.0	35.0	1,000	2,000
35	35FMN-BMT-A-TF	35FMN-BMTR-A-TB	35FMN-BMTTN-A-TF	35FMN-BMTTR-A-TB	35FMN-SMT-A-TF	34.0	37.0	38.0	36.0	1,000	2,000
36	36FMN-BMT-A-TF	36FMN-BMTR-A-TB	36FMN-BMTTN-A-TF	36FMN-BMTTR-A-TB	36FMN-SMT-A-TF	35.0	38.0	39.0	37.0	1,000	2,000
37	37FMN-BMT-A-TF	37FMN-BMTR-A-TB	37FMN-BMTTN-A-TF	37FMN-BMTTR-A-TB	37FMN-SMT-A-TF	36.0	39.0	40.0	38.0	1,000	2,000
38	38FMN-BMT-A-TF	38FMN-BMTR-A-TB	38FMN-BMTTN-A-TF	38FMN-BMTTR-A-TB	38FMN-SMT-A-TF	37.0	40.0	41.0	39.0	1,000	2,000
39	39FMN-BMT-A-TF	39FMN-BMTR-A-TB	39FMN-BMTTN-A-TF	39FMN-BMTTR-A-TB	39FMN-SMT-A-TF	38.0	41.0	42.0	40.0	1,000	2,000
40	40FMN-BMT-A-TF	40FMN-BMTR-A-TB	40FMN-BMTTN-A-TF	40FMN-BMTTR-A-TB	40FMN-SMT-A-TF	39.0	42.0	43.0	41.0	1,000	2,000

Material and Finish

Contact: Phosphor bronze, copper-undercoated, tin-plated (reflow treatment)
Housing: PA 6T, UL94V-0, black
Solder tab: Brass, copper-undercoated, tin-plated (reflow treatment)

RoHS2 compliance This product displays (LF)(SN) on a label.

Note: 1. The products listed above are supplied on embossed tape.

2. Contact JST for the top entry type headers with suction cap.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JST:](#)

[04FMN-BTRK-A\(N\)\(LF\)\(SN\)](#) [06FMN-BMTTN-A-TF\(LF\)\(SN\)-](#) [07FMN-BTK-A\(LF\)\(SN\);](#) [10FMN-BMTTN-A-TF\(LF\)\(SN\)-](#)
[11FMN-STK-A\(LF\)\(SN\);](#) [13FMN-STK-A\(LF\)\(SN\);](#) [14FMN-BMTR-A-TB\(LF\)\(SN\)](#) [15FMN-BMTTN-A-TF\(LF\)\(SN\)-](#)
[17FMN-BTK-A\(LF\)\(SN\);](#) [20FMN-BMTTR-A-TB\(LF\)\(SN\)-](#) [32FMN-BTK-A\(LF\)\(SN\)](#) [40FMN-BMTTN-A-TF\(LF\)\(SN\)](#)
[06FMN-SMT-A-TF\(LF\)\(SN\)-](#) [10FMN-BMTTR-A-TBT\(LF\)\(SN\)](#) [12FMN-SSTRK-A\(LF\)\(SN\);](#) [14FMN-BMTTR-A-](#)
[TB\(LF\)\(SN\)-](#) [14FMN-BTK-A\(LF\)\(SN\);](#) [15FMN-STK-A\(LF\)\(SN\);](#) [33FMN-SMT-A-TF\(LF\)\(SN\)](#) [05FMN-BTRK-](#)
[A\(N\)\(LF\)\(SN\)](#) [05FMN-SMT-A-TF\(LF\)\(SN\)](#) [10FMN-BMT-A-TFT\(LF\)\(SN\)-](#) [13FMN-SMT-A-TF\(LF\)\(SN\)-](#) [14FMN-BMTTN-](#)
[A-TF\(LF\)\(SN\)-](#) [15FMN-BMTTN-A-TFT\(LF\)\(SN\)-](#) [24FMN-SMT-A-TF\(LF\)\(SN\)-](#) [32FMN-BMTTR-A-TBT\(LF\)\(SN\)](#) [07FMN-](#)
[SMT-A-TF\(LF\)\(SN\)-](#) [20FMN-BTK-A\(LF\)\(SN\);](#) [30FMN-BMTTN-A-TF\(LF\)\(SN\)-](#) [05FMN-BMTTR-A-TBT\(LF\)\(SN\)-](#)
[08FMN-STK-A\(LF\)\(SN\);](#) [10FMN-STK-A\(LF\)\(SN\);](#) [16FMN-BMTTN-A-TF\(LF\)\(SN\)-](#) [25FMN-BTK-A\(LF\)\(SN\)](#) [37FMN-](#)
[SMT-A-TF\(LF\)\(SN\)](#) [09FMN-BTRK-A\(N\)\(LF\)\(SN\)](#) [12FMN-BMT-A-TFT\(LF\)\(SN\)-](#) [14FMN-SMT-A-TF\(LF\)\(SN\)-](#) [28FMN-](#)
[BTK-A\(LF\)\(SN\)](#) [04FMN-BTK-A\(LF\)\(SN\);](#) [04FMN-SMT-A-TF\(LF\)\(SN\)-](#) [08FMN-STRK-A\(N\)\(LF\)\(SN\)](#) [31FMN-SMT-A-](#)
[TF\(LF\)\(SN\)](#) [09FMN-BMTTN-A-TF\(LF\)\(SN\)-](#) [14FMN-BMTTR-A-TBT\(LF\)\(SN\)-](#) [19FMN-BTK-A\(LF\)\(SN\);](#) [33FMN-BTK-](#)
[A\(LF\)\(SN\)](#) [40FMN-SMT-A-TF\(LF\)\(SN\)](#) [04FMN-BMTTN-A-TF\(LF\)\(SN\)-](#) [05FMN-SMGB-A-TF\(LF\)\(SN\)-](#) [06FMN-BTK-](#)
[A\(LF\)\(SN\);](#) [08FMN-SSTRK-A\(LF\)\(SN\);](#) [25FMN-BMTTN-A-TFT\(LF\)\(SN\)-](#) [36FMN-BTK-A\(LF\)\(SN\)](#) [06FMN-BMT-A-](#)
[TFT\(LF\)\(SN\)-](#) [10FMN-BMTTN-A-TFT\(LF\)\(SN\)-](#) [14FMN-BMGUTR-A-TBT-](#) [16FMN-BMTTR-A-TB\(LF\)\(SN\)-](#) [20FMN-](#)
[BMTTN-A-TF\(LF\)\(SN\)-](#) [20FMN-BMTTR-A-TBT\(LF\)\(SN\)-](#) [22FMN-BTRK-A\(N\)\(LF\)\(SN\)](#) [13FMN-BMT-A-TF\(LF\)\(SN\)-](#)
[13FMN-BMTTN-A-TFT\(LF\)\(SN\)-](#) [40FMN-STK-A\(LF\)\(SN\)](#) [04FMN-SSTRK-A\(LF\)\(SN\);](#) [16FMN-STRK-A\(N\)\(LF\)\(SN\)](#)
[18FMN-BTK-A\(LF\)\(SN\);](#) [20FMN-SMT-A-TF\(LF\)\(SN\)-](#) [26FMN-BMTTR-A-TBT\(LF\)\(SN\)-](#) [34FMN-SMT-A-TF\(LF\)\(SN\)](#)
[10FMN-BMTTR-A-TB\(LF\)\(SN\)-](#) [15FMN-BTRK-A\(N\)\(LF\)\(SN\)](#) [18FMN-SMT-A-TF\(LF\)\(SN\)-](#) [30FMN-SMT-A-TF\(LF\)\(SN\)-](#)
[06FMN-BMTTN-A-TFT\(LF\)\(SN\)-](#) [07FMN-BMTTR-A-TBT\(LF\)\(SN\)-](#) [16FMN-BMT-A-TF\(LF\)\(SN\)-](#) [25FMN-BMTTR-A-](#)
[TBT\(LF\)\(SN\)-](#) [25FMN-BTRK-A\(LF\)\(SN\)](#) [28FMN-SSTRK-A\(LF\)\(SN\)](#) [30FMN-BTRK-A\(LF\)\(SN\)](#) [32FMN-SMT-A-](#)
[TF\(LF\)\(SN\)](#) [08FMN-BMTTN-A-TF\(LF\)\(SN\)-](#) [16FMN-BTRK-A\(N\)\(LF\)\(SN\)](#) [25FMN-BMTTN-A-TF\(LF\)\(SN\)-](#) [30FMN-BTK-](#)
[A\(LF\)\(SN\)](#) [32FMN-BMTR-A-TBT\(LF\)\(SN\)](#) [38FMN-SMT-A-TF\(LF\)\(SN\)](#) [08FMN-STK\(LF\)\(SN\);](#) [09FMN-SMT-A-](#)
[TF\(LF\)\(SN\)-](#) [11FMN-BTRK-A\(N\)\(LF\)\(SN\)](#) [12FMN-SMT-A-TF\(LF\)\(SN\)-](#) [17FMN-BTRK-A\(N\)\(LF\)\(SN\)](#) [26FMN-SMT-A-](#)
[TF\(LF\)\(SN\)-](#) [40FMN-BMT-A-TF\(LF\)\(SN\)](#) [40FMN-BMTTR-A-TB\(LF\)\(SN\)](#) [06FMN-SSTK-A\(LF\)\(SN\);](#) [13FMN-BMTTN-A-](#)
[TF\(LF\)\(SN\)-](#) [13FMN-BTRK-A\(N\)\(LF\)\(SN\)](#)