



Terminals & Splices > Automotive Terminals > AMPSEAL 16 CONTACTS



Terminal Type: **Socket**
Mating Pin Diameter: 1.59 mm [.062 in]
Terminal Transmits: 0 – 24 A (Low Power)
Wire Size: .52 – .823 mm²

[All AMPSEAL 16 CONTACTS \(35\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Clean Body

Contact Features

Contact Size	Size 16
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Typical Current Rating	13 A
Crimp Type	F-Crimp
Terminal Type	Socket
Mating Pin Diameter	1.59 mm[.062 in]
Interface Plating	Tin (Sn)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

--



Compatible Insulation Diameter Range	2.26 – 3.33 mm[.089 – .131 in]
Wire Size	.52 – .823 mm ²
Tab Length	21.6 mm[.85 in]

Usage Conditions

Insulation Option	Partially Insulated
Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Quantity	4000
Packaging Method	Reel

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits






as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-AM7801-CH8172 AMPSEAL 16 Housings	 TE Part # 1924463-1 PIN, SF, SIZE 16, 18-20 AWG, AU/SN	 TE Part # 91337-1 SIZE 16 PRO-CRIMPER ASSY.	 TE Part # 2151731-1 OCEAN_2.0_Applicator-S-100F130O-RSM
 TE Part # 91337-2 SIZE 16 PRO-CRIMPER DIE	 TE Part # 2151731-2 OCEAN_2.0_Applicator-S-100F130O-RSA	 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 5-2151731-1 OCEAN_2.0_Applicator-S-100F130O-RSM
 TE Part # 5-2151731-2 OCEAN_2.0_Applicator-S-100F130O-RSA	 TE Part # 7-2151238-7 OC-100F130O-752-CRIMPTOOLINGKIT	 TE Part # 7-2151731-7 OCEAN_2.0_SPARE_PART_KIT-100F130O	

Also in the Series | AMPSEAL 16

 Automotive Connector Caps & Covers (3)	 Automotive Connector Locks & Position Assurance(2)	 Automotive Housings(244)	 Automotive Terminals(35)
---	--	---	---



Connector Backshells(84)



Connector Seals & Cavity Plugs(4)



Data Connectivity Headers(2)




Data Connectivity Housings(3)



Other Automotive Connector Accessories(11)

Customers Also Bought




TE Part #1-160301-9
250 FASTON, REC., 10-12 AWG, PHBZ



TE Part #776537-3
AMPSEAL 16 Housings



TE Part #85113-1
MULTILOCK, CONNECTOR HOUSING



TE Part #927858-2
KONTAKTSTIFT 3,5 MM



TE Part #C616253001
55E0219-0.75-9(B01)

Documents

Product Drawings

SOC, SF, SIZE 16, 18-20 AWG, NI/SN

English

CAD Files

Customer View Model

ENG_CVM_776493-2_O.3d_igs.zip

English

Customer View Model



[ENG_CVM_776493-2_O.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_776493-2_O.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ICT Terminals and Connectors Catalogue](#)

English

CONNECTOR SELECTOR

English

Product Specifications

[Application Specification](#)

English