




Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Cable Connectors > Male-on-Wire Connector, Micro-MaTch



Connector System: **Cable-to-Board**
Number of Positions: **4**
Centerline (Pitch): **1.27 mm [.05 in]**
PCB Mount Retention: **Without**
PCB Mount Orientation: **Vertical**

[All Male-on-Wire Connector, Micro-MaTch \(19\)](#)

Features

Product Type Features

Ribbon Cable Connector Type	Male-On-Wire
Ribbon Cable Connector Header Type	Shrouded
Connector Product Type	Connector Assembly
Connector System	Cable-to-Board
Connector & Housing Type	Plug
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
PCB Mount Orientation	Vertical
Number of Rows	2

Electrical Characteristics

Insulation Resistance	1000 MΩ
-----------------------	---------



Operating Voltage	100 VAC
Body Features	
Daisy Chain	With
Primary Product Color	Red
Connector Profile	Standard
Contact Features	
Mating Tab Width	.7 mm[.028 in]
Mating Tab Thickness	.4 mm[.016 in]
Contact Type	Pin
Wire Contact Termination Area Plating Thickness	3 – 5 µm[118.11 – 196.85 µin]
Wire Contact Termination Area Plating Material Finish	Matte
Wire Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	3 – 5 µm[118.11 – 196.85 µin]
Contact Mating Area Plating Material	Tin
PCB Contact Termination Area Plating Material Finish	Matte
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	1.5 A
Termination Features	
Termination Method to Wire & Cable	Insulation Displacement (IDC)
Mechanical Attachment	
Mating Alignment	With
Contact Retention Type Within Housing	Press-Fit
PCB Mount Alignment	Without
PCB Mount Retention	Without
Mating Alignment Type	Polarization
Mating Retention	With
Mating Retention Type	Contact Friction
Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Housing Material	PBT GF



Centerline (Pitch)	1.27 mm[.05 in]
--------------------	-----------------

Dimensions

Connector Length	8.6 mm[.338 in]
Connector Height	6.8 mm[.27 in]
Compatible Insulation Diameter Range	.8 – 1 mm[.035 – .039 in]
Wire Size	.08 – .09 mm ²
Row-to-Row Spacing	2 mm[.059 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Rating	Recognized
Compatible With Agency/Standards Products	UL
Compatible With Approved Standards Products	UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	250
Packaging Method	Box & Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-M5833-F3492A Female-on-Board Connector, Top Entry	 TE Part # 7-215460-4 MICRO-MATCH FSID P	 TE Part # 215460-4 MICRO-MATCH FEM.SE	 TE Part # 100400-4 MICRO-MATCH FSID NP
 TE Part # 338070-4 MICRO-MATCH FEM.SE	 TE Part # 7-188431-4 MM 4P FIB SMD CONNECTOR	 TE Part # 7-100400-4 NOT POLARIZED,BOX A 250ST	 TE Part # 734024-1 Micro-MaTch ADAPTER, 4-24 POS.
 TE Part # 519708-1 TERMINATION PUSH	 TE Part # 677412-4 SEMI AUTO.MACHINE, MICRO-MATCH, 4-24 POS		

Also in the Series | Micro-MaTch Industrial

A collection of various board-in connectors, including black, yellow, and blue components with different pin configurations.

Board-In Connectors(21)

Four different types of connector contacts, including gold-plated and silver components.

Connector Contacts(4)

Three different types of insertion and extraction tools, including blue and orange handles.

Insertion & Extraction Tools(1)

A collection of pluggable I/O cable assemblies, including various cable lengths and connector types.

Pluggable I/O Cable Assemblies(52)

A collection of ribbon cable connectors, including black and silver components with different pin configurations.

Ribbon Cable Connectors(186)

Customers Also Bought

A collection of electronic components, including a black component with a white label and a silver component.

TE Part #6609021-4
2VB3=F7123 S0

A collection of red male-on-wire connectors with different pin configurations.

TE Part #8-215083-2
Male-on-Wire Connector, Micro-MaTch

A red MICRO-MATCH PBC.04P connector with multiple pins.

TE Part #7-215570-4
MICRO-MATCH PBC.04P

A silver and blue AV19 DPM 3A MOVE RING LED component.

TE Part #4-2213767-1
AV19 DPM 3A MOVE RING LED
WHITE 12V

A collection of electronic components, including a black component with a white label and a silver component.

TE Part #1-2176158-7
TLM 2512 1.0W R013 1% 100PPM 4K RL

A collection of silver contact pins with different pin configurations.

TE Part #166046-1
CONTACT, PIN, SZ 20, XI, CRIMP, 20-24

A black and silver CPF 0402 243K 0.1% 25PPM 1K RL component.

TE Part #6-1879216-4
CPF 0402 243K 0.1% 25PPM 1K RL

A black and silver Antenna 1/2 Wave Whip 2.4GHz RPS component.

TE Part #L9000023-01
Antenna 1/2 Wave Whip 2.4GHz RPS

Documents

Product Drawings
MICRO-MATCH MOW.04P

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_7-215083-4_U.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_7-215083-4_U.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-215083-4_U.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Micro-MaTch Catalog](#)

English

[Ribbon Cable Interconnect Solutions](#)

English

[Centerline Micro-Match Connector Series](#)

English

Product Specifications

[Application Specification](#)

English

[micro match miniature connector system](#)

English

Agency Approvals

[UL Report](#)

English