



PIDG

TE Internal #: 53550-1
Butt Splice, 12 – 10 AWG Wire Size, 3 – 6 mm² Wire Size, Serrated,
3.28 mm [.129 in] Barrel Inside Diameter, 5180 – 13100 CMA Wire
Size, PIDG, Splices

[View on TE.com >](#)

Terminals & Splices > Splices > PIDG Butt Splices



Splice Type: **Butt Splice**
Wire Size: **3 – 6 mm²**
Sealable: **No**
Splice Features: **Serrated**

[All PIDG Butt Splices \(25\)](#)

Features

Product Type Features

Splice Type	Butt Splice
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Insulation Support Sleeve Material	Copper
Insulation Material	PVF2
Product Weight	10 g
Splice Features	Serrated

Contact Features

Military Part Class	Class I
Terminal Plating Material	Tin-Lead
Contact Base Material	Copper
Barrel Type	Closed



Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	5180 – 13100 CMA
Compatible Insulation Diameter Range	5.59 mm[.22 in]
Barrel Inside Diameter	3.28 mm[.129 in]
Product Length	42.07 mm[.22 in]

Usage Conditions

Insulation Option	Fully Insulated
Operating Temperature Range	150 °C[302 °F]

Industry Standards

Government Qualified Splice	Yes
-----------------------------	-----

Packaging Features

Packaging Quantity	500
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (13% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 58433-3 PRO CR ASSY, RBY IS9252	TE Part # 58423-1 DIE, RBY IS9252	TE Part # 321286 PG BUTT 12-10	TE Part # 679300-1 1210 PIDG CRIMP HEAD
TE Part # 59824-1 TETRA-CRIMP PIDG PG FASTON 22-10 ASSY	TE Part # 59239-4 HHHT PIDG PG 12-10 ASSY	TE Part # 539691-2 ERGO DIE R.B.Y	TE Part # 2063030-1 SDE DIESET, RBY, UL
TE Part # 2217330-1 KIT, BTLI, 4 TON, NA	TE Part # 47808-6 DIES PIDG 12-10 DIE SET	TE Part # 169400 CERTI-LOK FRAME W/O DIES	TE Part # 169404 CERTI-LOK DIE
TE Part # 1SET191002R0000 TET CRIMP-HT			

Also in the Series | PIDG



Compression Connectors(17)



Crimp Wire Pins, Tabs & Ferrules(41)



Hand Crimping Tools(2)




Knife Disconnects(11)



Quick Disconnects(32)



Ring Terminals(589)



Spade Terminals(228)



Special Purpose Terminals(1)



Splices(40)

Customers Also Bought



TE Part #K1161759
Emergency Stop Switch ES-2002-T312-020B




TE Part #1393143-7
27E123=SOCKET,KRP,11,SCW,PLE



TE Part #2-1419106-7
27E895=SOCKET,K10,8,QC,POLY,NA



TE Part #5-1393144-5
K10P-11D15-12=K10/K20



TE Part #850845-000
TXR40AB00-1610BI



TE Part #2180143008
55A0811-20-9



TE Part #53408-1
PIDG PVF2 R 22-16COM22-18MIL 8



TE Part #2180333004
55A0811-16-9



Documents

Product Drawings

SPLICE BUTT PVF2 PIDG 12-10

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_53550-1_M.3d_igs.zip

English

Customer View Model

ENG_CVM_53550-1_M.3d_stp.zip

English

Customer View Model

ENG_CVM_53550-1_M.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.