



Terminals & Splices > Splices



Splice Type: **Butt Splice**
Wire Size: **2.62 – 6.64 mm²**
Sealable: **No**
Splice Features: **Serrated**

Features

Product Type Features

Splice Accessory Type	Splice
Splice Type	Butt Splice
Sealable	No
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Number of Serrations	6
Compatible With Wire & Cable Type	Discrete Wire

Body Features

Product Weight	2.259 g
Splice Features	Serrated

Contact Features

	100 μin
Terminal Plating Material	Tin

Contact Base Material	Copper
Barrel Type	Closed

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Outside Diameter	5.74 mm[.226 in]
Wire Size	5180 – 13100 CMA
Barrel Inside Diameter	3.28 mm[.129 in]
Terminal Material Thickness	.99 mm[.039 in]
Product Length	14.35 mm[.565 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	500
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 58545-1
SOLISTRAND 10-22 DIE ASSY



TE Part # 49935
DAHT SOLIS 22-10 ASSY




TE Part # 58546-1
PC 22-10 SOLISSPICE SPL I SHT



TE Part # 525693
DAHT SOLIS 22-10 ASSY



TE Part # 58545-3
SDE DIE ASSY. 22-10 SOLISTRAND



TE Part # 47814
DIES SOLIS 12-10 DIE SET



TE Part # 7-1377172-3
SMP 0-0032151-0



TE Part # 169400
CERTI-LOK FRAME W/O DIES

TE Part # 58545-4
SOLISTRAND 10-22 DIE ASSY.

Customers Also Bought



TE Part #3-647050-6
06P MTA100 HDR ASSY F/L HITEMP

TE Part #639637-000
202A174-4/86-0

TE Part #321280
SPLICE,SOLIS BUTT 14-12

TE Part #61021-1
SPLICE 18-16 AWG .0126 NPST

TE Part #52747
SPLICE,COPALUM PARA 4

TE Part #8-321198-1
SPLICE,SOLIS BUTT 26-22

TE Part #YDBC54H-2221PNV001
HERM RECP

TE Part #G4914ET22T1
NTC THERMISTOR ASSEMBLY

TE Part #363791-000
SCTM-76/33-A/U-C(100)

TE Part #1438238-9
101794

Documents

Product Drawings
SPLICE,SOLIS BUTT 12-10

English

CAD Files
Customer View Model
ENG_CVM_CVM_32151_P.2d_dxf.zip

English

3D PDF

3D

Customer View Model
ENG_CVM_CVM_32151_P.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_32151_P.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



SOLISTRAND - QRG

English

Agency Approvals

UL Report

English

UL Report

English