




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **.82 – 2.08 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Connection Capacity	Single
Compatible With Wire & Cable Type	Discrete Wire

Contact Features

Quick Disconnect Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Hole

Dimensions

Terminal Material Thickness	.85 mm[.033 in]
Product Length	21.33 mm[.84 in]
Compatible Insulation Diameter Range	.8 – 2 mm[.031 – .078 in]
Wire Size	.82 – 2.08 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Packaging Features

Packaging Quantity	500
Packaging Method	Loose Piece/Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 42559-1 250 FASTON TAB NPST	 TE Part # 90165-1 DAHT 250 FASTON REC 18-14 ASSY	 TE Part # 63771-1 187 FASTON TAB NPST	 TE Part # 63402-3 312 FASTON TAB BR
 TE Part # 61960-1 187 FASTON TAB NPST	 TE Part # 63953-1 187 FASTON TAB	 TE Part # 575046-1 DAHT 250 FASTON 22-14 ASSY	 TE Part # 626417-2 250 FASTON REC 22-18 AWG TPBR
 TE Part # 63402-2 312 FASTON TAB NPST			

Also in the Series | FASTON 250



Compression Connectors(4)



Crimp Terminal Housings(132)



Insertion & Extraction Tools(6)



Magnet Wire Terminals(1)



PCB Terminals(134)



Quick Disconnects(426)



Splices(4)

Customers Also Bought



TE Part #1SET411017R0000
PVC Wiring Duct: 2 meters, Gray Color, Flame-Retardant



TE Part #150346-2
110 MINI FASTON, REC., 24-20 AWG, TPBR



TE Part #41969-2
250 FASTON REC 22-18 AWG BR




TE Part #41274-1
250 FASTON, REC., 18-14 AWG, TPBR




TE Part #3-1437719-0
T01-0550-S03-FEMALE PLUG CONNECTOR SOLDE




TE Part #1089350001
RPS-6-250/2.0-4



TE Part #735052
110 FASTON SLEEVE REC. 1P NATURAL



TE Part #1SNA168146R0200
BRE-C-6



TE Part #1SNA566002R0000
CC-E-VA-2.2-SPE + CPT

Documents



Product Drawings

250 FASTON TAB 18-14 AWG TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_60006-2_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_60006-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_60006-2_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Agency Approvals

Agency Approval Document

English