

**BSTA078NN00420235000**

✓ ACTIVE

TE Internal #: BSA078N00420235000

Cable-to-Cable, 8 Position, Power &amp; Signal, Cable Mount (Free-Hanging), Electrodeposited Nickel, Zinc Alloy, PBT GF, Standard Circular Connectors

[View on TE.com >](#)

Connectors &gt; Circular Connectors &gt; Standard Circular Connectors

Connector System: **Cable-to-Cable**Connector Mounting Type: **Cable Mount (Free-Hanging)**Number of Positions: **8**Sealable: **No**Circuit Application: **Power & Signal**

## Features

### Product Type Features

Product Type	Housing Assembly
Connector System	Cable-to-Cable
Sealable	No
Circular Connector Type	Plug
Shell Type	Metal

### Configuration Features

Number of Positions	8
Number of Power Positions	4
Number of Signal Positions	4
Contacts Preloaded	No

### Electrical Characteristics

Operating Voltage	250 VAC, 630 VAC
-------------------	------------------

### Body Features

Environmental Protection Type	Sealed
-------------------------------	--------

Environmental Protection	IP67
Shell Plating Material	Electrodeposited Nickel
Shell Base Material	Zinc Alloy
Circular Connector Insulation Material Type	PBT GF

#### Mechanical Attachment

Mating Retention Type	Screw
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)
Mating Retention	With

#### Housing Features

Circular Connector Shell Size	23
Alignment Keyed	0°

#### Dimensions

Cable Diameter Range	9.5 – 14.5 mm [.37 – .57 in]
----------------------	------------------------------

#### Usage Conditions

IP Water Sealing Level	IP67
Operating Temperature Range	-20 – 130 °C [-4 – 266 °F]

#### Operation/Application

Durability Rating	500 Cycles
Circuit Application	Power & Signal
Shielded	Yes

#### Industry Standards

UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL

#### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)

Candidate List Declared Against: JAN 2024

(240)

SVHC &gt; Threshold:

Pb (3.5% in Component)

## Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not reviewed for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # BGC110N00001200000  
923 RECEPTACLE, ANGLED,  
ROTATABLE



TE Part # BGC110N00001216000  
923 RECEPTACLE, ANGLED,  
ROTATABLE



TE Part # BEA089N00000222000  
923 RECEPTACLE, SPEEDTEC-READY



TE Part # BEA120N00000200000  
923 RECEPTACLE, SPEEDTEC-READY



TE Part # BEA120N00000201000  
923 RECEPTACLE, SPEEDTEC-READY




TE Part # BEA120N00000241000  
923 RECEPTACLE, SPEEDTEC-READY




TE Part # BEA125N00000205000  
923 RECEPTACLE, SPEEDTEC-READY



TE Part # BFC110N00000207000  
923 RECEPTACLE, ANGLED



## Customers Also Bought





## Documents

### Product Drawings

#### 923 PLUG

English

---

### CAD Files

#### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_BSA078N00420235000\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_BSA078N00420235000\\_A.3d\\_jgs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_BSA078N00420235000\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

#### BSA078N00420235000

English

[fuer Datenblaetter, die online konfigurierbar sind](#)

German

---

### Product Specifications

German