




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **1 – 2.5 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Connection Capacity	Single
Compatible With Wire & Cable Type	Discrete Wire

Electrical Characteristics

Voltage Rating	250 V
----------------	-------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Flag
Contact Base Material	Phosphor Bronze
Terminal Plating Material	Tin
Crimp Type	F-Crimp



Barrel Type	Open
-------------	------

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Terminal Material Thickness	.41 mm[.016 in]
Product Length	14.2 mm[.559 in]
Compatible Insulation Diameter Range	2.5 – 3.81 mm[.098 – .15 in]
Wire Size	1 – 2.5 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	UL
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	3000
Packaging Method	Strip/Reel

Other

Line	Premier
------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-100645-3 250 FASTON,REC.,14-17AWG, PHBZ	 TE Part # 160862-8 FF FAH STECKH 8,0	 TE Part # 180397-2 250 FASTON,FLAG,REC.,17-14 AWG, TPBR	 TE Part # 180397-1 250 FASTON,FLAG,REC.,17-14 AWG, BR
 TE Part # 180397-5 250 FASTON,FLAG,REC.,17-14 AWG, TPPB	 TE Part # 1855631-1 HDM/FA SAPR.110F.180F LM CUT	 TE Part # 1855631-2 HDM/FA SAPR.110F.180F BENCH K CUT	 TE Part # 1855631-3 HDM/FA SAPR.110F.180F BENCH G CUT
 TE Part # 2151008-2 OCEAN_2.0_APPLICATOR-S-110F180F-SSA	 TE Part # 7-2151008-7 OCEAN_2.0_SPARE_PART_KIT-1110F180F		

Also in the Series | FASTON 250



Compression Connectors(4)



Crimp Terminal Housings(132)



Insertion & Extraction Tools(6)



Magnet Wire Terminals(1)



PCB Terminals(134)



Quick Disconnects(426)



Splices(4)


Customers Also Bought




TE Part #1534789-1
ADAPTER 90DEG 4/7POS



TE Part #5746861-4
9 POS HDF RCPT, MS




TE Part #1-1630019-0
Power Resistors: Aluminum Housed, HSA



TE Part #6-160432-0
250 FASTON REC 20-16 AWG TPBZ



TE Part #163301-8
MATENLOK PIN



TE Part #2-520979-2
ULTRA-FAST .110/.125 ASY REC 22-18 TPBR



TE Part #7-180984-0
250 FASTON BOOT FLAG REC. 1P NATURAL



TE Part #3142550001
D-SCE-6.4-50-S1-4



TE Part #1-180984-0
FASTON 250 FLAG BOOT NYLON NAT

Documents



Product Drawings

250 FASTON,FLAG,REC.,14-17AWG, LATON

English

CAD Files

Customer View Model

ENG_CVM_CVM_180464-5_AV.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_180464-5_AV.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_180464-5_AV.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

FASTON & FASTIN-FASTON conn. .250 srs. flag rec. ctc.

Application Specification

Agency Approvals

UL Report

English