

735052

 SUPERSEDED

FASTON | FASTON 110

TE Internal #: 735052

TE Internal Description: 110 FASTON SLEEVE REC. 1P NATURAL

[View on TE.com >](#)

Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings

Connector & Housing Type: **Receptacle**Number of Positions: **1**Terminal Orientation: **Straight**UL Flammability Rating: **UL 94V-2**Primary Product Color: **Natural**

Features

Product Type Features

Sealable	No
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Terminal Orientation	Straight
Contact Mating Retention	Without

Mechanical Attachment

Mating Alignment	Without
------------------	---------

Housing Features

Housing Material	Polyethylene
------------------	--------------

Dimensions

Product Length	24.4 mm [.961 in]
----------------	-------------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]
-----------------------------	-----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Product Compliance


For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Also in the Series | [FASTON 110](#)




Crimp Terminal Housings(13)



Insertion & Extraction Tools(1)



PCB Terminals(22)



Quick Disconnects(168)

Customers Also Bought

TE Part #2-1419104-1
T9AS1D22-24TE Part #521384-4
ASSY PL R/A RAST5 HEADER 04-ATE Part #150346-2
110 MINI FASTON,REC.,24-20 AWG, TPBRTE Part #41969-2
250 FASTON REC 22-18 AWG BRTE Part #60006-2
250 FASTON TAB 18-14 AWG TPBRTE Part #2176093-6
RP 2A 0.25W 10K2 0.1% 25PPM 1K RLTE Part #814777-000
202A111-3/42-0TE Part #316390-7
CAVITY PLUG FOR MINI M/LOCK

Documents

CAD Files

[3D PDF](#)
[3D](#)

Customer View Model

[ENG_CVM_CVM_735052_M.2d_dxf.zip](#)
[English](#)

Customer View Model

[ENG_CVM_CVM_735052_M.3d_igs.zip](#)
[English](#)

Customer View Model

[ENG_CVM_CVM_735052_M.3d_stp.zip](#)
[English](#)

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.