




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **2.62 – 4.17 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Low
-----------------	-----

Configuration Features

Connection Capacity	Single
Compatible With Wire & Cable Type	FLK

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Phosphor Bronze
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Extraction Force	7 – 100 Newton
Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Terminal Material Thickness	.41 mm[.016 in]
Product Length	22.5 mm[.886 in]
Compatible Insulation Diameter Range	3.6 – 4.3 mm[.141 – .169 in]
Wire Size	2.62 – 4.17 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Packaging Features

Packaging Quantity	1500
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

REPRESENTATION ONLY TE Part # 525651 DAHT POSITIVE LOCK 18-11 ASSY	TE Part # 724659-2 EXT TOOL FOR POSITIVE .250	TE Part # 216331-2 .250 POS.LOCK L.I.F	TE Part # 2151510-2 OCEAN_2.0_APPLICATOR-S-140F180F-RSA
TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	TE Part # 2837766-2 OCEAN-2.0-APPLICATOR-S-140F180F-RSA	KIT TE Part # 7-2151510-7 OCEAN_2.0_SPARE_PART_KIT-140F180F	KIT TE Part # 7-2837766-7 OCEAN_2.0_SPARE_PART_KIT-140F180F
KIT TE Part # 7-2266244-7 OC-140F180OV-CRIMPTOOLINGKIT			

Also in the Series | [Mark I](#)



Automotive Housings(1)



Automotive Terminals(4)



Crimp Terminal Housings(24)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(20)



Quick Disconnects(29)

Also in the Series | Positive Lock 250



Automotive Terminals(1)




Crimp Terminal Housings(190)



Insertion & Extraction Tools(3)




Insulation Boots & Sleeves(4)



Quick Disconnects(185)

Customers Also Bought



 TE Part #154717-6 PL 250 REC TERMINAL 14-11 AWG PTPB	 TE Part #293350-1 AMPMODU MOD I REC HOUSING-PA66-black	 TE Part #5053084023 RNF-100-3/16-9-SP	 TE Part #621056-000 D-142-52
 TE Part #1-968720-4 32pos MQS .63 header 90deg	 TE Part #D18609-000 B-155-07-F	 TE Part #1490189-5 CRIMPER, WIRE	TE Part #1SNA173438R2400 BJH14-2
TE Part #2119955-2 COMMERCIAL LUBRICATOR END FEED	TE Part #ZPF000000000112098 FICHE F 4PTS T.02 CLAV.N + CTS + OPTION		

Documents

Product Drawings

PL 250 REC TERMINAL 13-11 AWG TPPB

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_154717-4_AT.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_154717-4_AT.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_154717-4_AT.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



1654742_HOUSEHOLD_APPLIANCES_RAST5

English

Product Specifications

Application Specification

English