

Sensors > Temperature Sensors > RTD Sensors > RTD Sensor Elements



RTD Element Type: **Platinum Thin Film Temperature Element**

Tolerance Class: **Class C / F0.6**

Element Type: **Ceramic**

Element Material: **Platinum**

Lead Wire Style: **Ni/Au**

Features

Product Type Features

Wire/Cladding Type	Ni/Au
RTD Element Type	Platinum Thin Film Temperature Element
Element Type	Ceramic
Element Material	Platinum
Lead Wire Style	Ni/Au

Configuration Features

Electrical Connection	Open Ends
-----------------------	-----------

Mechanical Attachment

Wire Length	10 mm[.393 in]
-------------	----------------

Dimensions

Body Width	2 mm[.078 in]
Wire Diameter	.25 mm[.009 in]
Body Height	1.1 mm[.043 in]
Body Length	5 mm[.197 in]

Usage Conditions

T1 and T2 for TCR	0 and +100 °C
TCR at (T1 and T2)	3850 ppm/°C
Accuracy (at T_ref)	± .6 °C

Operating Temperature Range -50 – 600 °C[-58 – 1112 °F]

Operating Temperature (Max) 600 °C[1112 °F]

Other

Wire Count 2

Tolerance Class Class C / F0.6

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU Compliant

EU ELV Directive 2000/53/EC Not Yet Reviewed

China RoHS 2 Directive MIIT Order No 32, 2016 No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006 Current ECHA Candidate List: JUNE 2024 (241)

Candidate List Declared Against: JUNE 2024 (241)

Does not contain REACH SVHC

Halogen Content Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # NB-PTCO-166
Pt100, 2.0x5.0, Class C, PTFD101C1A0

Also in the Series | MEAS PTF



RTD Sensor Elements(53)

Customers Also Bought



TE Part #1-967622-3
JUN-POW-TIM GEH 12P




TE Part #1-967642-1
3POS MQS REC SEALED COD A



TE Part #2336682-1
2MM HM FEMALE ASSY, COL8



TE Part #350793-3
04P UMNL PIN HDR ASSY 94VO LF



TE Part #966067-3
FER,WIRE,PL SLV.,.50/20,L10,WHITE,LP




TE Part #5-102107-3
MOD IV PIN LP LF



TE Part #3-2176340-7
CRGCQ 0603 1M0 5%



TE Part #NB-PTCO-163
Pt1000, 2.0x2.3, Class C, PTFC102C1A0



TE Part #NB-PTCO-148
Pt100, 1.2x4.0, Class C, PTFM101C1G0

Documents

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_NB-PTCO-167_1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_NB-PTCO-167_1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_NB-PTCO-167_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Datasheet PTF-Family PTFC,PTFD,PTFF,PTFM](#)

English