

**BSTA108NN00580136000**

✓ ACTIVE

TE Internal #: BSA108N00580136000

Cable-to-Cable, Power & Signal, Cable Mount (Free-Hanging),  
Electrodeposited Nickel, Zinc Alloy, PBT GF, Size 23, Standard  
Circular Connectors[View on TE.com >](#)

Connectors &gt; Circular Connectors &gt; Standard Circular Connectors

Connector System: **Cable-to-Cable**Connector Mounting Type: **Cable Mount (Free-Hanging)**Sealable: **No**Circuit Application: **Power & Signal**Shell Plating Material: **Electrodeposited Nickel**

## Features

### Product Type Features

Product Type	Connector Assembly
Connector System	Cable-to-Cable
Sealable	No
Circular Connector Type	Plug
Shell Type	Metal

### Electrical Characteristics

Operating Voltage	630 VAC
-------------------	---------

### Body Features

Environmental Protection	IP67
Shell Plating Material	Electrodeposited Nickel
Shell Base Material	Zinc Alloy
Circular Connector Insulation Material Type	PBT GF

### Mechanical Attachment

Mating Retention Type	Speedtec (Triple Start Threaded)
-----------------------	----------------------------------

## Connector Mounting Type

Cable Mount (Free-Hanging)

## Housing Features

Circular Connector Shell Size

23

Alignment Keyed

0°

## Dimensions

Cable Diameter Range

9.5 – 14.5 mm [.37 – .57 in]

## Usage Conditions

Operating Temperature Range

-20 – 130 °C [-4 – 266 °F]

## Operation/Application

Durability Rating

500 Cycles

Circuit Application

Power &amp; Signal

Shielded

Yes

## Industry Standards

UL Flammability Rating

UL 94V-0

Compatible With Approved Standards Products

UL

## Product Compliance

For compliance documentation, visit the product page on [TE.com](https://TE.com)>

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024

(241)

Candidate List Declared Against: JAN 2024  
(240)SVHC > Threshold:  
Pb (3.5% in Component)Article Safe Usage Statements:  
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not reviewed for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these

limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Customers Also Bought




TE Part #284697-E  
SRCP 1,27 4 M 1 SMD 137 E1 094 \* GU-H\*



TE Part #ASA876N0085050A000  
617 PLUG, SPEEDTEC




TE Part #HGC422N00003200000  
723 htec receptacle, angled, speedtec



TE Part #1411006-1  
RESOLVER V23401-D1001-C801



TE Part #AUA013F01480150000  
623 PLUG, ANGLED



TE Part #BEA125M31000205000  
923 RECEPTACLE, SPEEDTEC-READY



TE Part #HSA427N00580100000  
723 HTEC PLUG, SPEEDTEC

## Documents

### Product Drawings

#### 923 PLUG, SHORT, SPEEDTEC

English

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_BSA108N00580136000\\_A.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_BSA108N00580136000\\_A.3d\\_jgs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_BSA108N00580136000\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

## Datasheets & Catalog Pages

BSTA108NN00580136000

Cable-to-Cable, Power & Signal, Cable Mount (Free-Hanging), Electrodeposited Nickel, Zinc Alloy, PBT GF, Size 23, Standard Circular Connectors



**BSA108N00580136000**

English

**fuer Datenblaetter, die online konfigurierbar sind**

German