



TE Internal #: BSA107N00590236000
Cable-to-Cable, Power, Cable Mount (Free-Hanging),
Electrodeposited Nickel, Zinc Alloy, PBT GF, Size 23, Shielded,
Plug, Standard Circular Connectors
[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Cable-to-Cable**
Connector Mounting Type: **Cable Mount (Free-Hanging)**
Sealable: **No**
Circuit Application: **Power**
Shell Plating Material: **Electrodeposited Nickel**

Features

Product Type Features

Product Type	Connector Assembly
Connector System	Cable-to-Cable
Sealable	No
Circular Connector Type	Plug
Shell Type	Metal

Electrical Characteristics

Operating Voltage	630 VAC
-------------------	---------

Body Features

Environmental Protection	IP67
Shell Plating Material	Electrodeposited Nickel
Shell Base Material	Zinc Alloy
Circular Connector Insulation Material Type	PBT GF

Mechanical Attachment

Mating Retention Type	Screw
-----------------------	-------



Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Circular Connector Shell Size	23
Alignment Keyed	0°
Dimensions	
Cable Diameter Range	14 – 17 mm[.55 – .67 in]
Usage Conditions	
Operating Temperature Range	-20 – 130 °C[-4 – 266 °F]
Operation/Application	
Durability Rating	500 Cycles
Circuit Application	Power
Shielded	Yes
Industry Standards	
UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (3.5% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these




limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # BEA116N00000200000
923 RECEPTACLE, SPEEDTEC-READY



TE Part # C0-0004-000-000
POSITIONING INSERT FOR 2 MM CONTACTS




TE Part # C0-0201-000-P00
CRIMPING TOOL MID-SIZE




TE Part # C0-0236-000-P00
DIGITAL CRIMPING TOOL, MID SIZE


Customers Also Bought




TE Part #DT04-2P
REC, 2P, GRY, N




TE Part #DT06-2S
PLG, 2P, GRY, N




TE Part #W2S
WedgeLocks: DEUTSCH DT




TE Part #0460-202-16141
DEUTSCH Solid Contacts



TE Part #282104-1
AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #114017-ZZ
SEALING PLUG, SIZE 12/16, WHT

Documents

Product Drawings
923 PLUG, SHORT

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_BSA107N00590236000_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_BSA107N00590236000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_BSA107N00590236000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[BSA107N00590236000](#)

English

[fuer Datenblaetter, die online konfigurierbar sind](#)

German

Product Specifications

German