




Connectors > Automotive Connectors > Automotive Housings



Connector System: **Wire-to-Wire**

Number of Positions: **3**

Centerline (Pitch): **2.54 mm [.1 in]**

Sealable: **Yes**

Mating Tab Width: **.64 mm [.025 in]**

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector System	Wire-to-Wire
Sealable	Yes

Configuration Features

Number of Positions	3
Number of Rows	1

Body Features

Primary Product Color	Black
Connector & Keying Code	A

Contact Features

Contact Size	.64mm
Mating Tab Width	.64 mm[.025 in]

Mechanical Attachment

Terminal Position Assurance	No
Strain Relief	Without
Mating Alignment Type	Keyed
Mating Alignment	With



Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Housing Material	Nylon 6/6 GF35
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Connector Height	15.85 mm[.624 in]
Product Width	15.85 mm[.624 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Compatible With Agency/Standards Products	SAE/USCAR-2 8/97
UL Flammability Rating	UL 94HB

Packaging Features

Packaging Quantity	25
Packaging Method	Package

Other

Connector Position Assurance Capable	Yes
--------------------------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold:



Octamethylcyclotetrasiloxane (D4) (.5% in Component Part)
Dodecamethylcyclohexasiloxane (D6) (.5% in Component Part)
Decamethylcyclopentasiloxane (D5) (.5% in Component Part)









Article Safe Usage Statements:
Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 638551-3 CONTACT,FEMALE,0.64MM,SN,18-20</p>	 <p>TE Part # 1326028-3 0.64MM FEMALE CONTACT,AU,18-20</p>	 <p>TE Part # 1326028-5 .64MM FEM CONT,AU,18-20,FORMED</p>	 <p>TE Part # 638551-1 CONTACT,FEMALE,0.64MM,SN,18-20</p>
 <p>TE Part # 1326028-2 0.64MM FEMALE CONTACT,AU, 22AWG</p>	 <p>TE Part # 638551-4 CONTACT,FEMALE,0.64MM,SN,22</p>	 <p>TE Part # 1326028-1 0.64MM FEMALE CONTACT,AU,18-20</p>	 <p>TE Part # 638551-2 CONTACT,FEMALE,0.64MM,SN,22</p>



TE Part # 1326028-4
0.64MM FEMALE CONTACT,AU, 22AWG

TE Part # 1326028-6
0.64MM FEMALE CONTACT,AU, 22AWG

Also in the Series

AMP 0.64 Connector System

Automotive Connector Caps & Covers (17)

Automotive Housings(26)

Automotive Terminals(12)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(5)

Customers Also Bought

TE Part #174952-1
070 MLC W-W PLUG HSG 20P

TE Part #T4112012041-000
M12 F, 4P GOLD A_CODE RA SHIELDED PG9

TE Part #184032-1
3 POS. PLUG ASSY, KEY A

TE Part #63564-1
SPLICE AMVAR 2000-5400 020BR

TE Part #184139-1
WIRE SEAL,RUBBER,SENSOR,BLUE

TE Part #184042-1
1 POS. PLUG ASSY, KEY A

TE Part #2345388-2
2POS,AMP MCP 2.8,REC HSG ASSY, SLD,COD 2

TE Part #368940-1
WIRE SEAL FOR ABS 25P(3.3-3.8)



Documents

Product Drawings
0.64MM,3 POSN SEALED PLUG ASSY
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1438454-1_B.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1438454-1_B.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1438454-1_B.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets
Instruction Sheet (U.S.)
English