



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board**

Number of Positions: **4**

Centerline (Pitch): **3.95 mm [.155 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	1

Body Features

Primary Product Color	Green
-----------------------	-------

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

--	--



Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	3.95 mm[.155 in]
--------------------	------------------

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Bag
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # 1318912-1 EP CONN LP REC	 TE Part # 1-1318301-4 3.96EP HDR ASSY 4(7)P NAT/TUBE	 TE Part # 1123721-2 ECONOMY POWER CONN REC CONT	 TE Part # 1-1123724-4 3.96EP HDR ASSY 4(7)P NATURAL
 TE Part # 1744494-4 04P EP-II HOUSING, YELLOW	 TE Part # 1744416-4 4 POS EP II HSG, GLOW WIRE	 TE Part # 6-1123723-4 3.96 EP HDR ASSY 4P(GREEN)	 TE Part # 1123721-1 EP CONN. REC CONTACT
 TE Part # 1-1565035-4 EP CONN HDR ASSY 4/6P SPECIAL	 TE Part # 1-1565036-4 3.96 EP CONN. HDR ASSY 4/8P NATURAL	 TE Part # 1-1717011-4 EP CONN.HDR ASSY 4/5POS SPECIA	 TE Part # 1565606-4 EP CONN HEADER ASS'Y 4/6P SPEC
 TE Part # 2-1123724-4 3.96EP HDR ASSY 4(7)P YELLOW	 TE Part # 2-1565035-4 EP CONN. HDR ASSY 4/6P SPECIAL (NO.4,5 P	 TE Part # 2-1717011-4 EP CONN.HDR ASSY 4/5P NATURAL (NO.3 POST	 TE Part # 3-1123724-4 3.96EP HDR ASSY 4(7)P BLUE
 TE Part # 4-1123724-4 3.96EP HDR ASSY 4(7)P RED	 TE Part # 5-1123724-4 3.96EP HDR ASSY 4(7)P BLACK	 TE Part # 5-1565035-4 EP CONN. HDR ASSY 4/6P SPECIAL WO.2,4 P	 TE Part # 5-1565606-4 EP CONN HEADER ASS'Y 4/6P BLACK

Also in the Series | Economy Power



Connector Contacts(15)

Connector Hardware(2)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(400)

Rectangular Connector Housings(1)

Rectangular Power Connectors(64)

Wire-to-Board Connector Assemblies & Housings(142)

Customers Also Bought

TE Part #134122-1
TERM, PIDG, R, IR, 14, M5

TE Part #2176378-1
RQ 0805 10R 0.1% 10PPM 5K RL

TE Part #1-2176379-5
RQ 0805 150R 0.1% 10PPM 5K RL

TE Part #2176381-9
RQ 0805 15K 0.1% 10PPM 5K RL

TE Part #3-2176379-1
RQ 0805 221R 0.1% 10PPM 5K RL

TE Part #3-2176382-9
RQ 0805 332K 0.1% 10PPM 5K RL

TE Part #6-2176380-7
RQ 0805 5K62 0.1% 10PPM 5K RL

TE Part #L9000017-01
Antenna 1/2 Wave Whip 2.4GHz SMA

TE Part #ARR-NF-NM-B
Arrestor Blkhd N Jack to N Plug

Documents



Product Drawings

3.96 EP PLUG HSG 4P(GREEN)

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6-1123722-4_P.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6-1123722-4_P.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6-1123722-4_P.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

Japanese

Economy Power (EP) Connector

Japanese